


te.com





FEATURES

- Temperature Sensor Included
- Amplified ±1.25V Signal Output
- 3.3 to 5.5Vdc Excitation Voltage
- Hermetically Sealed LCC Package
- Piezo-Ceramic Crystals, Shear Mode
- -40° to +125°C Operating Range
- Small PCB Footprint

APPLICATIONS

- Machine Health Monitoring
- Predictive Maintenance Installations
- Embedded Vibration Monitoring
- Impact & Shock Monitoring
- Data Loggers
- Bearing Installations
- Security Monitoring

830M1 TRIAXIAL CONDITION MONITORING ACCELEROMETER

- Triaxial Piezoelectric Accelerometer
- ±25g to ±2000g Dynamic Ranges
- Wide Bandwidth to 15,000Hz
- Superior Resolution to MEMS Devices
- Circuit Board Mountable, Reflow Solderable
- Low Cost, Superior Value

The Model 830M1 is a low cost, triaxial board mountable accelerometer designed for embedded condition monitoring and preventive maintenance applications. The piezoelectric (PE) accelerometer is available in ranges from ±25g to ±2000g and features a flat frequency response up to >15kHz in all three axes. The model 830M1 accelerometer three independent stable piezoceramic crystals in shear mode with low power electronics, sealed in a fully hermetic LCC package.

The PE technology incorporated in the 830M1 accelerometer has a proven track record for offering the reliable and long-term stable output required for condition monitoring applications. The accelerometer is designed and qualified for machine health monitoring and has superior resolution, dynamic range and bandwidth compared to MEMS devices.

An RTD temperature sensor is included inside the LCC package should the intended application require both a vibration and temperature sensor signal.

For single axis measurements, TE Connectivity also offers other accelerometer models with the same outstanding performance specifications.

CLICK HERE > CONNECT WITH A SPECIALIST

ABSOLUTE MAXIMUM RATINGS (1)

Parameter	Symbol	Min	Тур	Max	Unit	Notes/Conditions
Supply voltage ⁽²⁾	V_{dd}	1.5	3.3	5.5	V	
Storage temperature	Ts	-40		125	°C	
Shock limit (any axis)	G max			5,000	g	
ESD		-2		+2	kV	Human body model

⁽¹⁾ Maximum limits the device will withstand without damage

OPERATING RANGES & NOISE - ACCELEROMETER

(Unless otherwise specified, all parameters are measured at 24°C @ 3.3V applied)

Measurem ent Range	Sensitivity	Non- Linearity	Residual Noise ⁽¹⁾		Spectral Noi	se (mg/√Hz)	
(g)	mV/g	(%FSO)	(mg RMS)	10Hz	100Hz	1kz	10kHz
±25	50.0	±2	2.9	0.15	0.07	0.03	0.02
±50	25.0	±2	5.9	0.29	0.13	0.05	0.05
±100	12.5	±2	11.7	0.58	0.27	0.09	0.09
±200	6.3	±2	23.2	1.16	0.53	0.18	0.18
±500	2.50	±2	58.5	2.92	1.34	0.52	0.45
±1000	1.25	±2	117	5.84	2.68	1.04	0.90
±2000	0.63	±2	234	11.7	5.36	2.08	1.80

^{(1) 2}Hz to 10 kHz

ELECTRICAL SPECIFICATIONS

(Unless otherwise specified, all parameters are measured at 24°C @ 3.3V applied)

Parameters	Symbol	Min	Тур	Max	Unit	Notes/Conditions
Excitation voltage	V_{dd}	3.3		5.5	Vdc	
Zero g output voltage			$V_{dd}/2$			50% of applied voltage
Average supply current	lavg		200		μΑ	
Output impedance	Rout			100	Ω	
Warm-up time				1	Sec	

OPERATING SPECIFICATIONS - ACCELEROMETER

(Unless otherwise specified, all parameters are measured at 24°C @ 3.3V applied)

Parameter	Symbol	Min	Тур	Max	Unit	Notes/Conditions	
Full scale output			±1.25		V		
0.0g output voltage (bias V)			$V_{dd}/2$				
Frequency response		6		10k	Hz	±1db	
Frequency response		2		15k	Hz	±3db	
Resonant frequency		30k			Hz		
Transverse sensitivity				8	%	All Axes	
Calibration		CS-SENS-0100 NIST Traceable Amplitude Calibration at 80Hz					
		All parts are shipped with calibration data					

⁽²⁾ With 1.5V-2.5V excitation, full-scale range will be limited. So 3.3V min recommended.

OPERATING SPECIFICATIONS - RTD TEMPERATURE SENSOR (1)

(Unless otherwise specified, all parameters are measured at 0°C)

Parameter	Symbol	Min	Тур	Max	Unit	Notes/Conditions
RTD resistance	R ₀	997.81	1000	1002.20	Ω	@ 0°C
Tolerance		-0.12		+0.12	%	Class B
Calculated tolerance		±(0.4+0.007 x T)			°C	0 to +125°C
Calculated tolerance		±(0.4+0.028 x T)			°C	-40 to 0°C
Temperature coefficient	TCR	6100	6178	6240	ppm/K	
Temperature range		-40		125	°C	
Self-Heating coefficient ⁽²⁾	EK	1.4	1.7	2.0	mW/K	@ 0°C
Long term stability	ΔR		±0.1		%	1k hrs @ 150°C
Measurement current ⁽²⁾	I		0.2	5	mA	


⁽¹⁾The temperature sensor is located inside the sensor enclosure. As such, it provides the temperature of the sensor interior, not the ambient temperature around the sensor, nor the temperature of surface to which the sensor is mounted.

ENVIRONMENTAL SPECIFICATIONS


Parameter	Symbol	Min	Тур	Max	Unit	Notes/Conditions
Operating temperature		-40		125	°C	
Storage temperature		-40		125	°C	
Ambient humidity		0		100	%	
Ingress protection	IP	68				Hermetic Package
Media compatibility				l exposed Alumina Gold Au/Sn Sold		
Weight			3.3		grams	

 $^{^{(2)}\}mbox{Self}$ heating effects must be taken into account. See additional information in this data sheet.


BLOCK DIAGRAM



IR REFLOW TEMPERATURE PROFILE




DIMENSIONS




CONNECTION TABLE

Pin Number	Definition					
1	X axis output					
2	Y axis output					
3	Z axis output					
4	N/C					
5	N/C					
6	N/C					
7	GND					
8	RTD temp out					
9	V _{dd}					
10	N/C					
11	N/C					
12	N/C					
N/C connections -	N/C connections – do not connect to the circuit					




PC board solder pad layout and dimensions

TYPICAL ACCELEROMETER FREQUENCY RESPONSE CURVE



Graph 1

TYPICAL ACCELEROMETER THERMAL SHIFT OF SENSITIVITY



Graph 2

MOUNTING CONSIDERATIONS

Accelerometers are used to measure vibration and motion of various pieces of equipment and their components. To obtain the most faithful reproduction of the movements, a solid mounting method is required. The model 830M1 is designed to surface mount on a PC board with the primary attachment being the connection solder pads. Although it is recommended that several of the contacts (pins 4-6 & 10-12) not be connected to any part of the electrical circuit, mating solder pads can be added to the PC board but then left unconnected. Soldering all contacts of the accelerometer will provide the most solid mounting and best measurement results.


Rigid support for the accelerometer PC board will also help to improve the quality of measurement signals. Ultimately, the accelerometer must move at the same frequencies and displacements as the object of interest. PC board mounting that's not rigid enough will introduce unwanted noise and resonant frequencies into the measurement signal.

Figure 1 shows an example of a poorly mounted accelerometer. With no support close to the sensor, the PC board will flex and vibrate at its own resonant frequency much like a trampoline. This will introduce unwanted resonant peaks into the frequency range of interest making accurate data collection difficult.

Figure 2 shows a better mounting design that provides support very close to the sensor and helps to eliminated unwanted vibrations and noise. If the PC board is mounted on standoffs, locate at least two standoffs as close to the accelerometer as possible. This will help stabilize the accelerometer mounting surface and help to ensure that faithful vibration and motion get transferred to the sensor.

Figure 3 shows the addition a rigid mounting block directly between the accelerometer PC board and the vibrating object. This design provides good coupling. Use a rigid adhesive on both mating surfaces of the block for good mechanical coupling.

Figure 4 shows the PC board attached directly to the vibration source. Use a rigid adhesive to improve the transmission of high frequency vibrations and acoustic energy. Soft or elastic adhesives (pressure sensitive tapes, RTVs, pliable glues, etc) tend to dampen and absorb higher frequency excitations. Don't use them.




ORIENTATION CONSIDERATIONS

Accelerometers are designed to do unidirectional motion sensing. A single axis accelerometer will be sensitive to motion and acceleration in a single direction only. The 830M1 is able to sense and measure motion and acceleration in all three orthogonal axes (X, Y, Z) and provides analog voltage outputs that represent the signal magnitude in each axis. The accelerometer must be properly oriented during assembly into the application to ensure that it will accurately sense the magnitude of vibration and motion in the proper axes.

As shown in the detailed dimension drawing, each sensing axis is aligned to be parallel with the external surfaces of the accelerometer package. When the sensor is designed into an application, it's position must be oriented to align with the desired measurement directions of the customer product.

There are many places in an application where alignment errors can appear. The 830M1 is mounted on a PC board and must be carefully aligned to it. The PC board is part of a subsystem and must be carefully aligned there also. And finally, the subsystem is part of the overall product and must be aligned to that. Each of these mounting interfaces can be a source of mis-alignment errors and when summed can become significant.

For the 830M1 accelerometer, there are two types of alignment errors – rotational and tilt. Figures 5 & 6 show how these occur.



Both types of misalignment errors result in incorrect output voltages for vibration amplitude. The output error will be proportional to the cosine or 1-cosine of the error angle θ .

In figure 5, if the acceleration or vibration is along the X axis, a rotational misalignment error will decrease the X axis signal by the cosine of the error angle and increase the Y axis signal by 1-cosine of the error angle. The Z axis signal will not change.

In figure 6, if acceleration is again along the X axis, and the X axis is tilted, then the error will again decrease the X axis signal by the cosine of the error angle and increase the Z axis signal by 1-cosine of the error angle. The Y axis signal will not change.

ACCELEROMETER OPERATION AT REDUCED VOLTAGES

The 830M1 accelerometer is designed to provide the specified operation with the applied power voltage in the range of 3.3 to 5.5 VDC. The sensor can also provide limited operation with applied voltages down to 1.5V. The only parameter affected by a reduced input voltage is the maximum output amplitude for each g range.

The internal amplifier is designed to have a constant gain for each g range and will produce a maximum output signal of ±1.25 V for that range. At input voltages less than 2.8 V, the output voltage span will be the same as the power voltage. The sensor will retain the stated sensitivity level, but the output will be clipped at the power supply voltages shown by this formula:

$$g_{\text{max}} = g_{\text{spec}} \times \frac{V_{\text{app}}}{2.5}$$

 g_{max} = Measurement g range with applied voltage between 1.5 – 2.5V

g_{spec} = specified g range when applied voltage >2.5V

 V_{app} = applied power voltage (1.5 – 2.5V)






Figure 5

g range (V _{dd} >2.8V)	Effective g range (V _{dd} =1.5V)
±25	±15
±50	±30
±100	±60
±200	±120
±500	±300
±1000	±600
±2000	±1200

BUILT-IN RTD TEMPERATURE SENSOR TRANSFER FUNCTION





TEMPERATURE SENSOR SELF HEATING EFFECT

For accurate temperature measurement it is recommended to use a small current to avoid self-heating of the temperature sensing element. The temperature error caused by excessive measurement current can be calculated using:

$$\Delta T = \frac{I^2 x R}{EK}$$

 ΔT = Sensor output deviation from true temperature

I = Resistor current

R = RTD resistance

EK = Self-heating coefficient

TEMPERATURE SENSOR ELECTRICAL CHARACTERISTICS

The characteristics of the nickel RTD temperature sensor are specified as per DIN 43760. The large Temperature Coefficient of Resistance (TCR) of the RTD (6178 ppm/K) offers greater sensitivity than other types of RTDs. The electrical characteristics can be described by these equations:

$$R(T) = R_0(1+aT+bT^2+cT^4+dT^6)$$

R = RTD resistance value

T = Applied temperature

Coefficients: $a = 5.485 \times 10^{-3}$

 $b = 6.650 \times 10^{-6}$

 $c = 2.805 \times 10^{-11}$

 $d = -2.000 \times 10^{-17}$

$$T(R) = a'+b'(1+c'R)^{1/2}+d'R^5+e'R^7$$

T = True temperature

R = Measured resistance

Coefficients: a' = - 412.6

b' = 140.41

c' = 0.00764

 $d' = 6.25 \times 10^{-17}$

 $e' = -1.25 \times 10^{-24}$

TEMPERATURE SENSOR TOLERANCES


Tolerances for the nickel RTD are industry standard class B which is $\pm 0.12\%$ for resistance at 0°C. This is equivalent to a temperature accuracy of ± 0.3 °C. To calculate tolerance at other temperatures, use these formulae:


From -40°C to 0°C - Tolerance =
$$\pm (0.4 + 0.028|T|)$$

From 0°C to 125°C - Tolerance =
$$\pm (0.4+0.007|T|)$$

SIMPLE INTERFACE CIRCUITS CONVERT TEMPERATURE TO LINEAR VOLTAGE

The resistive divider or constant current circuits will provide a low accuracy linear voltage output representing temperature.







Graph 5

INTERFACE CIRCUIT WITH A HIGH ACCURACY OUTPUT


The operational amplifier circuit uses a Wheatstone bridge front end to improve measurement resolution. The addition of R5 improves the circuit linearity.




$$\underline{V_{\text{out}}} = \frac{\left[\frac{R_{\text{RTD}} \times R5}{R_{\text{RTD}} + R5}\right] \times \underbrace{V_{\text{dd}}}_{\text{R}}}_{\text{R1} + \left[\frac{R_{\text{RTD}} \times R5}{R_{\text{RTD}} + R5}\right]} \times \left[1 + R4 \times \left[\frac{1}{R2} + \frac{1}{R3}\right]\right] - \frac{R4 \times \underbrace{V_{\text{dd}}}_{\text{R2}}}_{\text{R2}}$$




PACKAGING OPTIONS





ORDERING INFORMATION



Suffix	G Range	Packaging Part Number				
		Tray (50 pcs)	Tape & Reel (400 pcs)			
0025	25g	20011422-00	20011422-01			
0050	50g	20011423-00	20011423-01			
0100	100g	20011424-00	20011424-01			
0200	200g	20011425-00	20011425-01			
0500	500g	20011426-00	20011426-01			
1000	1000g	20018122-00	20018122-01			
2000	2000g	20019427-00	20019427-01			

CLICK HERE > CONNECT WITH A SPECIALIST

NORTH AMERICA

Tel +1 800 522 6752

EUROPE

Tel +31 73 624 6999

ASIA

Tel +86 0400 820 6015

te.com/sensors

TE Connectivity, TE, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2021 TE Connectivity Corporation. All Rights Reserved.

01/2021

