

K-12-M23 M9/2,0-E00/M23 F8 - Connector in molded plastic on both sides



1619292

<https://www.phoenixcontact.com/gb/products/1619292>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector in molded plastic on both sides, Straight, plastic molded, number of positions: 12, type of locking: Screw locking mechanism, Straight, plastic molded, cable length: 2 m, shielded: yes, color of outer sheath: orange RAL 2003

Your advantages

- Our standard: robust halogen-free PUR cable
- Simple and safe: 100% electrically tested and assembled ready for use
- Designs with preassembled cables on one or both sides
- High flexibility: customer-specific assemblies and cable lengths can be supplied

Commercial data

Item number	1619292
Packing unit	1 pc
Minimum order quantity	2 pc
Sales key	ABRDFG
Product key	ABRDFG
Catalog page	Page 217 (C-2-2019)
GTIN	4046356835084
Weight per piece (including packing)	363.4 g
Weight per piece (excluding packing)	350.807 g
Customs tariff number	85444290
Country of origin	DE

K-12-M23 M9/2,0-E00/M23 F8 - Connector in molded plastic on both sides



1619292

<https://www.phoenixcontact.com/gb/products/1619292>

Technical data

Product properties

Product type	Signal and power cable
--------------	------------------------

Connector

Connector specifications

Type	Straight, plastic molded
Housing material	Die-cast zinc
Type of locking	Screw locking mechanism
Degree of protection	IP67, when in locked state
No. of pos.	12
Direction of rotation	Standard
Insertion/withdrawal cycles	50
Contact resistance	< 0.3 mΩ
Max. current	8 A
Voltage	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV
Ambient temperature (operation)	-40 °C ... 105 °C

Cable specifications

Cable type	RSL9YSLC11Y
Shielded	yes
Cable structure	4 x 2 x 0.25 mm ² + 2 x 0.5 mm ²
Cable structure (AWG)	24 AWG/4pr + 20 AWG/2c
External cable diameter	8.00 mm
Outer sheath, material	TPU
Material wire insulation	PP
External sheath, color	orange RAL 2003
Test voltage	1 kV
Rated current	9 A
Smallest bending radius, fixed installation	40 mm
Smallest bending radius, movable installation	60 mm
Ambient temperature (operation) for fixed installation	-40 °C ... 80 °C
Ambient temperature (operation) for flexible installation	-20 °C ... 60 °C

Connector specifications (second page)

Type	Straight, plastic molded
------	--------------------------

K-12-M23 M9/2,0-E00/M23 F8 - Connector in molded plastic on both sides



1619292

<https://www.phoenixcontact.com/gb/products/1619292>

Electrical properties

Nominal current I_N	9 A
-----------------------	-----

Cable/line

Cable length	2 m
--------------	-----

K-12-M23 M9/2,0-E00/M23 F8 - Connector in molded plastic on both sides




1619292

<https://www.phoenixcontact.com/gb/products/1619292>


Drawings

Dimensional drawing



On the female side

Dimensional drawing




Pin side

K-12-M23 M9/2,0-E00/M23 F8 - Connector in molded plastic on both sides

1619292

<https://www.phoenixcontact.com/gb/products/1619292>

Schematic diagram




Socket pin assignment

K-12-M23 M9/2,0-E00/M23 F8 - Connector in molded plastic on both sides

1619292

<https://www.phoenixcontact.com/gb/products/1619292>

Schematic diagram




Pin assignment of pin

K-12-M23 M9/2,0-E00/M23 F8 - Connector in molded plastic on both sides

1619292

<https://www.phoenixcontact.com/gb/products/1619292>

Circuit diagram



Contact assignment of M23 plugs/sockets

K-12-M23 M9/2,0-E00/M23 F8 - Connector in molded plastic on both sides



1619292

<https://www.phoenixcontact.com/gb/products/1619292>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1619292>



EAC

Approval ID: 19060508



UL Listed

Approval ID: E335019-20140707

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Power	48 V	5 A	-	-
Signal	48 V	2 A	-	-



cUL Listed

Approval ID: E335019-20140707

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Power	48 V	5 A	-	-
Signal	48 V	2 A	-	-

K-12-M23 M9/2,0-E00/M23 F8 - Connector in molded plastic on both sides

1619292
<https://www.phoenixcontact.com/gb/products/1619292>

Classifications

ECLASS	
ECLASS-13.0	27060106
ETIM	
ETIM 9.0	EC003250
UNSPSC	
UNSPSC 21.0	26121600

K-12-M23 M9/2,0-E00/M23 F8 - Connector in molded plastic on both sides



1619292

<https://www.phoenixcontact.com/gb/products/1619292>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(b), 6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b884233b-bd42-40a0-bb42-de7dfd49fd8

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk