

668B - COBALT STEEL BIMETAL SAW BLADES | 668B.12



Norm :

NF E 73-072, ISO 2336-1, DIN 6494

Description

- Characteristics:
 - 668B.8: for thick semi-hard steels - thickness recommended: 6 - 25 mm.
 - 668B.10: for special or alloy steels - thickness recommended: 3 - 6 mm.
 - 668B.12: for stainless steel, copper - thickness recommended: 1 - 3 mm.
- Blade in cobalt steel: higher heat resistance, reduced teeth wear.
- Equal performance throughout blade lifecycle.
- Enhanced flexibility and neater cut.
- Suited to all materials.
- Blade length 300 mm.

Information

[g] 160