

Part Number : [442626321](#)
Product Description : 5.33mm Pitch Crimp Terminal, Power Blade, Select Gold Strips over Tin
Series Number : 44262
Status : Active
Product Category : Crimp Terminals

Documents & Resources

Drawings

[442626321_sd.pdf](#)


[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006 
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	44262
Description	5.33mm Pitch Crimp Terminal, Power Blade, Select Gold Strips over Tin
Application	Power, Wire-to-Wire
Product Name	N/A
UPC	822350975209

Electrical

Current - Maximum per Contact	50.0A
Voltage - Maximum	600V AC

Physical

Durability (mating cycles max)	500
Gender	Male
Material - Metal	Copper
Material - Plating Mating	Gold
Net Weight	1.352/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.79mm max.
Wire Size (AWG)	10, 12
Wire Size mm ²	N/A

Solder Process Data

Max-Duration	40
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	3
Max-Temp	260

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for 14-10 AWG Power Contact Terminals	<u>638195400</u>
Mini-Mac Applicator for Power Contact Crimp Terminals, Single 12-10 AWG and Double 14+14 AWG	<u>638326600</u>