



**FAG****61805-HLC**

Deep groove ball bearing

Deep groove ball bearing 618, single row,
steel sheet metal cageSchaeffler ID:
0554553600000

Technical information



Your current product variant

Logistical code	HLC	-
Sealing	Without	Not sealed
Cage	J	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Without	Bearing not greased
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	25 mm	Bore diameter
D	37 mm	Outside diameter
B	7 mm	Width
C _r	4.300 N	Basic dynamic load rating, radial
C _{0r}	2.940 N	Basic static load rating, radial
C _{ur}	132 N	Fatigue load limit, radial
n _G	28.000 1/min	Limiting speed
n _{gr}	13.900 1/min	Reference speed
m	22 g	Weight



Mounting dimensions

$d_{a\ min}$	27 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	35 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	0,3 mm	Maximum fillet radius

Dimensions

$r_{\ min}$	0,3 mm	Minimum chamfer dimension
D_1	33,2 mm	Shoulder diameter outer ring
d_1	28,2 mm	Shoulder diameter inner ring

Temperature range

$T_{\ min}$	-30 °C	Operating temperature min.
$T_{\ max}$	120 °C	Operating temperature max.

Calculation factors

f_0	13,9	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed