

ZCKE235

limit switch head ZCKE - steel roller lever plunger
- +120 °C



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJD31H29 ZCKJD35H29 ZCKJ4H7 ZCKJ9H7 ZCKJ2 ZCKJ6H29 ZCKJD35H7 ZCKJ11H29 ZCKJD35 ZCKJ1 ZCKJ4 ZCKJD37 ZCKJD31H7 ZCKJD37H29 ZCKJD39H7 ZCKJ5H7 ZCKJ6 ZCKJ5 ZCKJ4H29 ZCKJ7H29 ZCKJ5H29 ZCKJD31 ZCKJ1H29 ZCKJ21H7 ZCKJ8 ZCKJ41H7 ZCKJ2H7 ZCKJ8H7 ZCKJD37H7 ZCKJ6H7 ZCKJD39H29

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKJ7
ZCKJ1H7
ZCKJ7H7
ZCKJ21H29
ZCKJ2H29
ZCKJ11
ZCKJ41
ZCKJ41H29
ZCKJ9H29
ZCKJ11H7
ZCKJ21
ZCKJD39
ZCKJ9
ZCKJ8H29

Movement of operating head	Linear
Type of operator	Roller lever plunger spring return metal
Type of approach	Lateral approach, 1 direction

Complementary

Switch actuation	By 30° cam
Positive opening	With
Net weight	0.195 kg
Head material	Metal

Environment

Ambient air temperature for operation	10...120 °C
Ambient air temperature for storage	10...120 °C
Environmental characteristic	High temperature

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------