

DOW CORNING® 817 Mirror Adhesive

FEATURES

- Non-corrosive, odorless, ready to use gun grade sealant which reacts with air moisture
- Excellent unprimed adhesion on most glasses, metals and mirror coatings
- Outstanding resistance to heat and humidity
- High modulus to reduce the sealant consumption
- Resistant to ozone, ultra-violet radiation and temperature extremes

High modulus neutral silicone sealant

APPLICATIONS

• DOW CORNING 817 Mirror Adhesive is a one-part silicone sealant for internal fixation of mirrors, coated glass or metal panels onto various substrates.

TYPICAL PROPERTIES

Specification writers: These values are not intended for use in preparing specifications. Please contact your local Dow Corning sales representative prior to writing specifications on this product.

Test method*	Property	Unit	Value
	Cure system		Neutral
	Application temperature	$^{\circ}\mathrm{C}$	+5 to +40
		°F	+41 to +104
	Service temperature range	°C	-50 to +100
		°F	-58 to +212
	Working time	minutes	29
CTM97B	Specific gravity	g/ml	1.43
CTM062	Slump	mm	≤ 3
	12*12*50mm size T.A. joint (ISO 8339)	
CTM99E	Hardness (Shore A)		38
	Young modulus	MPa	1.2

^{*} CTM: Corporate Test Method, copies of CTMs are available on request.

HOW TO USE

Surface preparation

Ensure that surfaces to be sealed are clean, dry, sound and free from grease, dust and other contaminants which could impair adhesion.

Surfaces can be cleaned and degreased by wiping with a suitable solvent such as DOW CORNING®

R40 Universal Cleaner on a clean oil-and lint-free cloth before application of sealant. Check to ensure that the mirror has been evenly coated, is protected by lacquer and is free of scratches.

Note: When using any solvent, always provide adequate ventilation. Avoid heat, sparks and open flames. Use solvent resistant gloves. Observe and follow all precautions listed on

solvent container label.

Priming

For specific advice, please refer to the DOW CORNING® Primers' Guide or contact one of Dow Corning's Regional Service Centers for technical assistance.

Sealant application

The sealant is ready to use. Apply 10mm wide strips vertically on the back of the mirror in 100mm intervals. Then press the mirror onto the surface, preserving a constant bead thickness of 2mm for optimum cure and mechanical grab. Support the mirror for a minimum of 24 hours using adhesive tapes. This will ensure good contact and a minimum of displacement.

Air should be allowed to circulate freely around the edges of the mirror thereby allowing the sealant to cure.

Clean-up

Excess sealant may be cleaned off tools and non-porous surfaces whilst in an uncured state using DOW CORNING R40 Universal Cleaner. If sealant is misapplied to porous substrates, it should be left until just cured, and then removed by peeling, cutting or other mechanical means. Care should be taken not to damage plastic or coated surfaces.

HANDLING PRECAUTIONS

PRODUCT SAFETY
INFORMATION REQUIRED FOR
SAFE USE IS NOT INCLUDED.
BEFORE HANDLING, READ
PRODUCT AND SAFETY DATA
SHEETS AND CONTAINER
LABELS FOR SAFE USE,
PHYSICAL AND HEALTH
HAZARD INFORMATION. THE
SAFETY DATA SHEET IS
AVAILABLE FROM YOUR LOCAL
DOW CORNING SALES
REPRESENTATIVE.

USABLE LIFE AND STORAGE

When stored in cool, dry conditions below 30°C (86°F) in the original unopened containers, DOW CORNING 817 Mirror Adhesive has a usable life of 12 months from the date of production.

PACKAGING

DOW CORNING 817 Mirror Adhesive is supplied in 310ml cartridges packed in boxes of 12.

LIMITATIONS

Do not use DOW CORNING 817
Mirror Adhesive on bituminous
substrates, substrates based on natural
rubber, choloroprene or EPDM or on
building materials which might bleed
oils, plasticisers or solvents. Do not
use DOW CORNING 817 Mirror
Adhesive in a totally confined space
because the sealant requires
atmospheric moisture to cure.
DOW CORNING 817 Mirror
Adhesive is not recommended for use
in submerged applications or in

applications where physical abuse of abrasion is likely to occur.

When used with safety mirrors (single pane mirrors laminated with a plastic film at the back to prevent shattering of the glass when broken), first check adherence of DOW CORNING 817 Mirror Adhesive on the plastic film.

This product is not suitable for areas where food contact is likely.

DOW CORNING 817 Mirror Adhesive is not recommended for structural glazing or insulated glazing applications.

This product is neither tested nor represented as suitable for medical or pharmaceutical uses.

HEALTH AND ENVIRONMENTAL INFORMATION

To support customers in their product safety needs, Dow Corning has an extensive Product Stewardship organization and a team of Health, Environment and Regulatory Affairs specialists available in each area.

For further information, please consult your local Dow Corning representative.

WARRANTY INFORMATION - PLEASE READ CAREFULLY

The information contained herein is offered in good faith and is believed to be accurate. However, because conditions and methods of use of our products are beyond our control, this information should not be used in substitution for customer's tests to ensure that Dow Corning's products are safe, effective, and fully satisfactory for the intended end use. Dow Corning's sole warranty is that the product will meet the Dow Corning sales specifications in effect at the time of shipment. Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted. Dow Corning specifically disclaims any other express or implied warranty of fitness for a particular purpose or merchantability. Unless Dow Corning provides you with a specific, duly signed endorsement of fitness for use, Dow Corning disclaims liability for any incidental or consequential damages. Suggestions of use shall not be taken as inducements to infringe any patent.