



### Main

|                           |                              |
|---------------------------|------------------------------|
| Range                     | Exiway                       |
| Product name              | Exiway Light                 |
| Product or component type | Emergency light fitting      |
| Device application        | Anti-panic lighting          |
| Function                  | Standard                     |
| Supply                    | Maintained<br>Non-maintained |
| Number of batteries       | 1 x 6.4 V 1.5 Ah LiFePO4     |
| Light source              | 25 x integral LED 0.3 W      |
| Visibility distance       | 20 m                         |
| Light source colour       | Neutral                      |

### Complementary

|                                |  |
|--------------------------------|--|
| [Ue] rated operational voltage | 230 V 50/60 Hz   |
| Power consumption in VA        | 24.2 VA non-maintained<br>23.5 VA maintained   |
| Power consumption in W         | 1 W non-maintained<br>2.3 W maintained   |
| Electrical insulation class    | Class II   |
| LED lifespan                   | 100000 h   |
| Autonomy                       | 1 h<br>1.5 h<br>2 h<br>3 h   |
| Charging time                  | 12 h   |
| Luminous flux                  | Emergency condition: 500 lm for 1 h<br>Emergency condition: 400 lm for 1.5 h<br>Emergency condition: 300 lm for 2 h<br>Emergency condition: 250 lm for 3 h |

|                  |                                  |
|------------------|----------------------------------|
|                  | Maintained mode: 230 lm          |
| Local signalling | LED                              |
| Material         | Thermoplastic self-extinguishing |
| Device mounting  | Surface wall<br>Surface ceiling  |
| Height           | 112 mm                           |
| Width            | 229 mm                           |
| Depth            | 32 mm                            |
| Net weight       | 0.42 kg                          |

## Environment

|                                       |   |
|---------------------------------------|---|
| IP degree of protection               | IP65  |
| IK degree of protection               | IK09  |
| Ambient air temperature for operation | 0...40 °C   |
| Product certifications                | CE<br>ENEC  |
| Standards                             | EN 60598-1<br>EN 60598-2-22<br>EN 62034<br>EN 62471<br>UL 94 V2 |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope)                 |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        | <a href="#">End of Life Information</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|