



Technical data


NU211EAT2X

Single row cylindrical roller bearings

Single row cylindrical roller bearing, floating, separable, polyamide cage


ULTAGE®

VISUAL (S)



NU211EAT2X

Single row cylindrical roller bearings



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	55 mm
D - External diameter	100 mm
B - Bearing/Inner ring width	21 mm
E - Upper roller diameter	90 mm
F - Under roller diameter	66 mm
rs - Min fillet radius	1,5 mm
r1s - Min fillet radius	1,1 mm
Radial clearance class	CN
Mass	0,675 kg

PRODUCT PERFORMANCE

C - Dynamic load	102000000 mN
C0 - Static load	98500000 mN



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

NU211EAT2X

Single row cylindrical roller bearings

PRODUCT PERFORMANCE

Cu - Fatigue limit load	12000000 mN
N lim - Oil lubrication limit speed	53400 °/s
N lim - Grease lubrication limit speed	37800 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	61,5 mm
da max - Small face shoulder max diameter	65 mm
db min - Min inner ring GO diameter	68 mm
Da max - Max shoulder diameter OR	92 mm
ra max - Max fillet radius	1,5 mm
r1a - Max fillet radius	1 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = Fr$$

Equivalent static radial load

$$P_0 = Fr$$

