



All High Pin Count Header (45)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM,
HOUSING

Customers Also Bought

TE Part #6-1393104-7
KRPA-14AG-24=KRPA

TE Part #6-534206-5
30 MODII VRT DR CE 100/115

TE Part #84953-4
1MM FPC HORZ.TOP CONT.ASSY 4P

TE Part #776262-5
14POS,PIN DIA 1.3,HDR ASSY,
180DEG,COD 5

TE Part #9-2176305-4
RP 1E 0.1W 1K0 0.1% 25PPM 5K RL

TE Part #4-1437416-0
SSB7FP120201=SSB STRIP 7/16, 1

TE Part #7-2176307-2
RP 1E 0.1W 68K1 0.1% 25PPM 5K RL

TE Part #5520259-4
MJ,TE,8P,TRAYS

TE Part #796449-1
PLUG ASSY,CPC,17-14,REV SEX

TE Part #4-1437658-5
8PCV-12-006=#8 TRIBARRIER TERM

Documents

Product Drawings

025/090 56POS CAP ASSY H TIN

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-1318751-0_J1.3d_igs.zip

English



Customer View Model

[ENG_CVM_CVM_2-1318751-0_J1.3d_stp.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-1318751-0_J1.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Crimping of 025 Receptacle Contact](#)

Japanese

[Application Specification](#)

Japanese