



AZ 16-02ZVK-M16

- 3 cable entries M 16 x 1.5
- Thermoplastic enclosure
- Double-insulated
- 52 mm x 90 mm x 30 mm
- Universal coding
- Long life
- High level of contact reliability with low voltages and currents
- Insensitive to soiling
- Slotted holes for adjustment, circular holes for location

Data

Ordering data

Product type description	AZ 16-02ZVK-M16
Article number (order number)	131154699
EAN (European Article Number)	8905236103810
eCl@ss number, version 12.0	27-27-26-02
eCl@ss number, version 11.0	27-27-26-02
eCl@ss number, version 9.0	27-27-26-02
ETIM number, version 7.0	EC002592
ETIM number, version 6.0	EC002592

Approvals - Standards

Certificates	cULus CCC
--------------	--------------

General data

Standards	EN ISO 13849-1 EN ISO 14119 EN IEC 60947-5-1
Coding level according to EN ISO 14119	Low
Working principle	electromechanical
Housing material	Plastic, glass-fibre reinforced thermoplastic, self-extinguishing
Gross weight	115 g

General data - Features

Ejection force	Yes
Number of actuating directions	3
Number of safety contacts	2
Number of cable glands	3

Safety classification

Standards	EN ISO 13849-1
Performance Level, up to	c
Category	1
B _{10D} Normally-closed contact (NC)	2,000,000 Operations
Note	Electrical life on request.
B _{10D} Normally-open contact (NO)	1,000,000 Operations
Note	at 10% I _e and ohmic load
Mission time	20 Year(s)

Safety classification - Fault exclusion

Please note:	Can be used when fault exclusion for dangerous damage to the 1-channel mechanism is permissible and sufficient protection against manipulation is guaranteed.
Performance Level, up to	d
Category	3

Note	for 2-channel use and with suitable logic unit.
------	---

Mission time	20 Year(s)
--------------	------------

Mechanical data

Mechanical life, minimum	1,000,000 Operations
--------------------------	----------------------

Positive break travel	8 mm
-----------------------	------

Positive break force per NC contact, minimum	10 N
--	------

Positive break force, minimum	20 N
-------------------------------	------

Actuating speed, maximum	2 m/s
--------------------------	-------

Mounting	Screws
----------	--------

Type of the fixing screws	2x M6
---------------------------	-------

Mechanical data - Connection technique

Cable entry	3 x M16 x 1,5
-------------	---------------

Termination	Screw terminals
-------------	-----------------

Cable section, minimum	0.25 mm ²
------------------------	----------------------

Cable section, maximum	2.5 mm ²
------------------------	---------------------

Note	All indications including the conductor ferrules.
------	---

Allowed type of cable	solid single-wire solid multi-wire flexible
-----------------------	---

Mechanical data - Dimensions

Length of sensor	30 mm
------------------	-------

Width of sensor	52 mm
-----------------	-------

Height of sensor	90 mm
------------------	-------

Ambient conditions

Degree of protection	IP67
----------------------	------

Ambient temperature	-30 ... +80 °C
---------------------	----------------

Storage and transport temperature	-40 ... +85 °C
-----------------------------------	----------------

Permissible installation altitude above sea level, maximum	2,000 m
--	---------

Ambient conditions - Insulation values

Rated insulation voltage U_i	500 V
--------------------------------	-------

Rated impulse withstand voltage U_{imp}	6 kV
---	------

Overvoltage category	III
----------------------	-----

Degree of pollution	3
---------------------	---

Electrical data

Thermal test current	10 A
----------------------	------

Required rated short-circuit current	1,000 A
--------------------------------------	---------

Switching element	2 NC contact
-------------------	--------------

Switching principle	slow action, positive break NC contact
---------------------	--

Maximum switching frequency	4,000 /h
-----------------------------	----------

Material of the contacts, electrical	Silver
--------------------------------------	--------

Electrical data - Safety contacts

Voltage, Utilisation category AC-15	230 VAC
-------------------------------------	---------

Current, Utilisation category AC-15	4 A
-------------------------------------	-----

Voltage, Utilisation category DC-13	24 VDC
-------------------------------------	--------

Current, Utilisation category DC-13	4 A
-------------------------------------	-----

Electrical data - Auxiliary contacts

Voltage, Utilisation category AC- 230 VAC
15

Current, Utilisation category AC- 4 A
15

Voltage, Utilisation category DC- 24 VDC
13

Current, Utilisation category DC- 4 A
13

Scope of delivery

Scope of delivery Slot covers for dust-proof covering of the openings not in use

Ordering code

Product type description:
AZ 16-(1)ZV(2)K-(3)-(4)-(5)

(1)	
without	1 NO contact/1 NC contact
02	2 NC contact
03	3 NC contact
12	1 NO contact/2 NC contacts
(2)	
without	Ejection force
R	Latching force 30 N
(3)	
G24	with LED (only available for version with one NO and one NC contact)
(4)	
M16	cable entry M16
M20	Cable entry M20
ST	Connector M12, 4 pole, bottom
STL	Connector M12, 4 pole, left

STR	Connector M12, 4 pole, right
(5)	
2254	Latching force 5 N
1762	Front mounting
1637	Gold-plated contacts


Pictures

Product picture (catalogue individual photo)




ID: kaz16f01
 | 471.8 kB | .jpg | 165.806 x 268.817 mm - 470 x 762 px - 72 dpi
 | 115.4 kB | .png | 74.083 x 119.944 mm - 210 x 340 px - 72 dpi
 | 74.5 kB | .jpg | 76.2 x 123.472 mm - 216 x 350 px - 72 dpi

Dimensional drawing basic component




ID: laz16g01
 | 28.1 kB | .cdr |
 | 3.1 kB | .png | 74.083 x 51.506 mm - 210 x 146 px - 72 dpi
 | 62.3 kB | .jpg | 352.778 x 245.886 mm - 1000 x 697 px - 72 dpi

Switch travel diagram



ID: kaz16s02
 | 20.1 kB | .cdr |
 | 2.1 kB | .png | 74.083 x 26.106 mm - 210 x 74 px - 72 dpi
 | 56.2 kB | .jpg | 352.778 x 123.472 mm - 1000 x 350 px - 72 dpi

Diagram



ID: k2o--k01
 | 48.8 kB | .jpg | 352.778 x 125.236 mm - 1000 x 355 px - 72 dpi
 | 2.3 kB | .png | 74.083 x 26.458 mm - 210 x 75 px - 72 dpi

The details and data referred to have been carefully checked. Images may diverge from original. Further technical data can be found in the manual. Technical amendments and errors possible.

Generated on: 26/12/2024, 7:37 am