

HDMI™-Cable

00205239 Ultra High Speed HDMI™ Cable, Certified, Plug - Plug, 8K, alu, 2.0 m



Highlighttext:

- For the ultra-high-speed transmission of digital audio and video data between e.g. gaming console, Blu-ray player, satellite receiver and TV set
- High-tech cable sheath reinforced with aramid fibres: especially sturdy, heat-resistant and long-lasting
- For perfect, high-resolution ultra-HD cinema quality with 7680x4320 (8K) pixels
- Resolutions of 8K @ 60 Hz / 4K @ 120 Hz for delay-free gaming enjoyment
- Dynamic HDR allows every image to be reproduced with the best individual results for depth, sharpness, brightness, contrast and extended colour space
- Supports network connections via HDMI™ for reduced cabling
- eARC supports the most advanced audio formats without additional audio cables
- High-quality materials and shielded lines for excellent picture and sound quality without interference
- Superior premium quality with respect to workmanship and performance
- Robust metal plug with the best shielding for reliable signal transmission
- Flexible materials guarantee optimum kink protection and prevent cable breakage
- Gold-plated plug with low contact resistance for secure signal transmission
- The inner conductor is made of copper which ensures best transmission properties

Technical characteristics:

- Colour: Grey
- Productline: Prime Line
- Shade of colour: Black, Grey
- Quality: Prime
- Bandwidth: 1200 MHz
- Connection: HDMI™ Plug
- Data Transfer Rate: 48 Gbit/s
- Max. Resolution: 8k
- Refresh rate: 120 Hz/60 Hz
- Technology: Dynamic HDR/ Extended audio return channel (eARC)/ HDMI™ Ethernet Channel (HEC)
- Type of Shielding: Fully Shielded
- Additional Functions: 3D Transmission, HDTV-suitable
- Material: Full metal
- Special Feature: Gold-Plated/Textile cable
- Version: Ultra High Speed with Ethernet
- Length: 2 m
- Licensed for: HDMI™ Ultra High Speed
- Licensed from/by: HDMI.org

Delivery:

- 1 ultra high speed HDMI™ cable

 4 047443 438959	Brand	Item-no.	VE	MB	Quanti
	hama	00205239	40	1	1