




Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FPC Connectors



Centerline (Pitch): **.5 mm [ .02 in ]**

Mating Retention Type: **Zero Insertion Force (ZIF)**

PCB Mount Orientation: **Right Angle**

Contact Mating Location: **Top**

Termination Method to PCB: **Surface Mount**

Features

Product Type Features

|                                   |                                |
|-----------------------------------|--------------------------------|
| PCB Connector Type                | PCB Mount Receptacle           |
| Connector & Contact Terminates To | Flexible Printed Circuit (FPC) |
| Connector Product Type            | Connector Assembly             |
| Connector System                  | Flex-to-Board                  |
| FPC Actuator Type                 | Stuffer                        |

Configuration Features

|                                   |             |
|-----------------------------------|-------------|
| Compatible With Wire & Cable Type | FFC, FPC    |
| Number of Rows                    | 1           |
| PCB Mount Orientation             | Right Angle |
| Number of Positions               | 44          |

Electrical Characteristics

|                   |         |
|-------------------|---------|
| Operating Voltage | 250 VAC |
|-------------------|---------|

Body Features

|                       |         |
|-----------------------|---------|
| Primary Product Color | Natural |
|-----------------------|---------|

Contact Features

|                                                         |                   |
|---------------------------------------------------------|-------------------|
| Contact Current Rating (Max)                            | .5 A              |
| Contact Shape & Form                                    | Single Beam       |
| PCB Contact Termination Area Plating Material Thickness | .025 μm[.984 μin] |
| Contact Layout                                          | Inline            |



|                                                |                   |
|------------------------------------------------|-------------------|
| Contact Base Material                          | Phosphor Bronze   |
| PCB Contact Termination Area Plating Material  | Gold              |
| Contact Type                                   | Socket            |
| Contact Mating Area Plating Material Thickness | .025 μm[.984 μin] |
| Contact Mating Location                        | Top               |
| Contact Mating Area Plating Material           | Gold Flash        |

Termination Features

|                           |               |
|---------------------------|---------------|
| Termination Method to PCB | Surface Mount |
|---------------------------|---------------|

Mechanical Attachment

|                         |                            |
|-------------------------|----------------------------|
| Connector Mounting Type | Board Mount                |
| Mating Alignment        | With                       |
| PCB Mount Retention     | With                       |
| PCB Mount Alignment     | Without                    |
| Mating Retention Type   | Zero Insertion Force (ZIF) |

Housing Features

|                    |                              |
|--------------------|------------------------------|
| Housing Material   | LCP (Liquid Crystal Polymer) |
| Centerline (Pitch) | .5 mm[.02 in]                |

Dimensions

|                              |                   |
|------------------------------|-------------------|
| Connector Width              | 5.1 mm[.2 in]     |
| Accepts Flex Cable Thickness | .3 mm[.012 in]    |
| Connector Height             | 2.05 mm[.08 in]   |
| Connector Length             | 27.43 mm[1.08 in] |

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature Range | -40 – 85 °C[-40 – 185 °F] |
|-----------------------------|---------------------------|

Operation/Application

|                     |        |
|---------------------|--------|
| Circuit Application | Signal |
|---------------------|--------|

Identification Marking

|                                |         |
|--------------------------------|---------|
| Circuit Identification Feature | Without |
|--------------------------------|---------|

Packaging Features

|                    |             |
|--------------------|-------------|
| Packaging Method   | Tape & Reel |
| Packaging Quantity | 2000        |



Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Not Yet Reviewed                                                                                                              |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUN 2018 (191)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought



TE Part #51863-7  
TERMINAL,PIDG R IR 18 6




TE Part #745781-4  
09 MSFL RCPT RA 318 (IN,FM)



TE Part #1055688-1  
2367 5001 54, VERT PLUG




TE Part #1-1123823-1  
EP IP PLUG NATURAL




TE Part #1-1123722-5  
3.96 EP PLUG HSG 5P(NATURAL)



TE Part #102320-1  
UNIVERSAL HEADER LATCH



TE Part #1064333-1  
9950 2200 23



TE Part #331003-005  
55A1111-22-9-9



TE Part #5-747912-4  
25 PLUG SOLDER CUP STD DUPL, R



TE Part #4-2176245-8  
CRGS1206 5% 8K2

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_4-1734839-4\_C.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1734839-4\_C.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1734839-4\_C.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FPC Connector Family

English

1-1773959-7-FPC-Connectors-CN

English

Product Specifications

Product Specification

English