

## FEATURES

- **Graphite material:** Provides excellent thermal conductivity and chemical resistance
- **Maximum operating pressure of 20000 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 650 °C:** Ensures performance in extreme heat conditions
- **Rotary speed of 30 m/s:** Capable of handling high-speed operations
- **9.5 mm section:** Offers a robust sealing solution

## RS PRO 8m Graphite Gland Packing, 9.5mm Section

RS Stock No: 606-573



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

RS PRO offers a high-quality graphite gland packing designed for sealing applications in industrial environments. This product is ideal for use in high-pressure and high-temperature settings, providing reliable performance and durability.

## General Specifications

Maximum Operating Pressure	20000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	30 m/s
Section	9.5 mm
Sub Type	Gland Packing

## Mechanical Specifications

Length	8 m
Material	Graphite

## Operation Environment Specifications

Maximum Operating Temperature	650 °C
-------------------------------	--------

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------