

Product datasheet

Specifications



Cable tie, Thorsman installation material, 120x2.5mm, clear

IMT46403

Main

product range	Thorsman
Range of product	Thorsman installation material
product type	Cable tie
colour	Clear
quantity per package	Set of 100

Complementary

Minimum tightening diameter	3 mm
Maximum tightening diameter	27 mm
Condition of use	Indoor
resistance to tearing	Resistance to tearing: 80 N
Material	PA (polyamide) 6.6 UV-stabilised
Length	120 mm
Width	2.5 mm
Thickness	1.1 mm
Net weight	0.031 kg
Market segment	Small commercial

Environment

Environmental characteristic	Fire resistance needle flame 30 s conforming to IEC 60695-11-5
Flame retardance	Self-extinguishing conforming to UL 94 V2
Ambient air temperature for operation	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	9.5 cm
Package 1 Length	21 cm
Package 1 Weight	37.2 g
Unit Type of Package 2	BAG
Number of Units in Package 2	100

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	7 cm
Package 2 Width	50 cm
Package 2 Length	70 cm
Package 2 Weight	3.77 kg
Unit Type of Package 3	S35
Number of Units in Package 3	200
Package 3 Height	15 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	8.32 kg

Contractual warranty

Warranty	18 mois
----------	---------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration
Halogen content performance	Halogen free product
PVC free	Yes

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No