



GE
Lighting



GLS

TU 42W HALO A/CL/E27 240V GE TWBX
2/16TR

63931

Product information

GE's HaloGLS range is a direct replacement for regular incandescent lamps offering a crisp white light. Environmentally friendly solution for those who prefer light quality associated with incandescent bulbs.

- Last twice as long and consume up to 30% less electricity than corresponding incandescent lamps.
- Provide instant-on, full light output at start-up and lumens are maintained throughout the life of the product.
- Unlike some compact fluorescent products, these lamps are 100% retrofit with the incandescent lamps they replace.
- Can be used with dimming switches.
- Environmentally friendly with no lead or mercury.
- Up to 2,000 hours life
- Excellent colour rendering, light close to natural (100% CRI)

- More than 90% lumen maintenance over life
-

Product data

Cap/Base	E27
Bulb Shape	GLS
Bulb Diameter [mm]	50
Dimming Capability	Yes
Maximum Overall Length [mm]	89.5
DUN Code	10043168639313
EAN Code	0043168639316
Net weight per piece [g]	25
Gross weight per piece [g]	34
Brand	General Electric (GE)

Performance data

Nominal power [W]	42
Nominal lamp voltage [V]	240
Nominal lumens [lm]	630
Rated efficacy [lm/W]	15
Colour temperature [K]	2800
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	2000
Coil type	2CC-8
Energy efficiency class (EEC)	D
Weighted energy consumption [kWh/1000h]	43.65

Logistic data

Pack Quantity	16
Inner pack type	TWIN BOX
Outer pack type	TRAY OUTER
Layer quantity	384 EUR, 480 UK
Layer quantity EUR	384
Layer quantity UK	480
Pallet quantity EUR (PC)	4224
Pallet quantity UK (PC)	5280
Outer case size	200 x 169 x 91 (mm)
Product status	Available while stock lasts

Application areas



Home



Hospitality

Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Halogen Lamps Spectrum Catalogue \(PDF\)](#)

[GLS, Candle, Spherical Lamps Data sheet \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)