

Multi Tool LXT®

DTM53

18V

DTM53 is a multi tool powered by an 18V LXT Li-Ion battery

Designed to be compatible with OIS accessories. By implementing a brushless motor this model offers higher work efficiency and improved ability to move freely and easily with a slimmer grip. Features constant speed control. Equipped with a tool-less accessory clamp and the oscillating rate can be adjusted between 6,000 and 20,000 min⁻¹.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Orbits per Minute	6000 - 20000 min ⁻¹
Oscillation Angle	2 x 1,6 °
Pad size (triangle)	93 x 93 x 93 mm
Sound Pressure Level (L _{pA})	80 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,7 - 2,6 kg
Product Dimensions (L x W x H):	329 x 80 x 120 mm
Brushless Motor	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Sound Power Level (L _{WA})	88 dB(A)
Product net weight	1,3 kg
Vibration Level, Sanding	4,3 m/s ²
Vibration Uncertainty (K Factor),	1,5 m/s ²

User benefits

- Tool-less blade change for fast blade installation and removal
- 12 Angle settings at every 30° from 0° to 360°
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Soft start for smooth start-ups
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makita.dk



Related products

Other

User manual

Parts drawing