



FLAMESTAT HIGH VIS STRETCH SOFTSHELL ANORAK CLASS 3 4019 FSS

ART. NO: 300561

Softshell stretch material / Windproof and water repellent / Storm hood designed for perfect fit over a helmet with 3 adjustment possibilities – front edge, top and side width / Front placket opening with half-length two-way zip to top of collar and concealed snap fastening / Large inside chest pocket that runs all the way to the sides - with zip at the top and three compartments / Pocket is accessible both from front of jacket and from the vertical zip chest pockets / Full-length zip at front side concealed under placket with snap fastening and velcro / Concealed D-ring at chest / 2 microphone holders at chest / Loops at shoulders to attach armband / 2 concealed zip sleeve pockets for mobile phone – straight pocket on right side and vertical pocket on left side / Large kangaroo pocket at lower back with zip openings at both sides / Adjustable sleeve ends with velcro / Adjustable drawstring at waist and bottom / Extended back / Loops for attaching separate crotch strap 301602 / Approved according to EN 61482-1-2 APC 2, EN 61482-1-1 ELIM 23 cal/cm² EBT 28 cal/cm² / EN ISO 11612 A1 A2 B1 C2 F1, EN 1149-5, EN ISO 20471 class 3 and EN 13758-2 UPF 40+ UV protection. Fabric is approved UPF 500+ UV protection / Leasing-laundry tested according to ISO 15797 / OEKO-TEX® certified.

Material: Stretch 47% modacrylic, 37% cotton, 12% polyurethane, 2% polyamide, 1% anti-static fibre, 1% elastane. Inherent flame protection. In transition to PFAS free.

Weight: 365 g/m².

Color: F171 High vis Yellow/Navy

Size: XS-3XL



STANDARD
100
PPE
SE 23-311
HDE

PRO U6

EN 11612 EN 1149-5 IEC 61482-2 EN 20471

FRISTADS®

SIZES MAY VARY BETWEEN COLORS
Print date: 2025-09-04