



Main miniature circuit breaker (SHU), 1-pole, E 25A, 230/400 V (block with L1, L2, L3)

Model	
product brand name	SENTRON
product designation	Miniature circuit breaker
design of the product	Main miniature circuit breaker
General technical data	
number of poles	1
design of pole	1P
tripping characteristic class	E
mechanical service life (operating cycles) typical	20 000
overvoltage category	IV
degree of pollution	3
Voltage	
insulation voltage (Ui) rated value	690 V
surge voltage resistance rated value	6 kV
supply voltage with single-phase operation at AC rated value	230 V
operational current	
• at 30 °C rated value	25 A
• at 40 °C rated value	23.75 A
• at 50 °C rated value	22.5 A
• at 55 °C rated value	21.875 A
• at AC rated value	25 A
Supply voltage	
supply voltage at AC	230 V
operating voltage rated value	
• minimum	110 V
• maximum	440 V
supply voltage frequency rated value	50 Hz
Protection class	
protection class IP	IP40, with connected conductors
Breaking Capacity	
switching capacity current	
• rated value	25 kA
• according to EN 60898 rated value	25 kA
Dissipation	
power loss [W] for rated value of the current at AC in hot operating state per pole	6.5 W
suitability for operation	Residential buildings/infrastructure
Product details	
product component	

<ul style="list-style-type: none"> outgoing feeder via spring-loaded terminal 	Yes
<ul style="list-style-type: none"> infeed at box terminal 	Yes
product feature	
<ul style="list-style-type: none"> properties for main switches in accordance with EN 60204-1 	Yes
<ul style="list-style-type: none"> sealable 	Yes
Display and operation	
display version for switch position indicator	OFF = green, ON = red
Connections	
connectable conductor cross-section of spring-loaded terminal finely stranded with core end processing	
<ul style="list-style-type: none"> minimum 	2.5 mm ²
<ul style="list-style-type: none"> maximum 	16 mm ²
connectable conductor cross-section of the box terminal	
<ul style="list-style-type: none"> solid minimum 	2.5 mm ²
<ul style="list-style-type: none"> solid maximum 	50 mm ²
<ul style="list-style-type: none"> stranded minimum 	2.5 mm ²
<ul style="list-style-type: none"> stranded maximum 	50 mm ²
position of power supply cord	Stipulated by installation in the lower section of the meter panel
Mechanical Design	
height	151.3 mm
depth	89.5 mm
depth of the enclosure	76.3 mm
number of modular width units	1.5
fastening method	Busbar
fastening method other	on 40-mm busbar system in compliance with DIN 43870 Part 2
net weight	1 305 g
Environmental conditions	
shock resistance	30 g, at least 3 impacts, impact duration 11 ms
vibration resistance according to IEC 60068-2-6	2 g, 20 frequency cycles 5 to 150 to 15 Hz
ambient temperature during operation	
<ul style="list-style-type: none"> minimum 	-25 °C
<ul style="list-style-type: none"> maximum 	55 °C
ambient temperature during storage	
<ul style="list-style-type: none"> minimum 	-40 °C
<ul style="list-style-type: none"> maximum 	70 °C
Approvals Certificates	
General Product Approval	other



[Confirmation](#)



[Confirmation](#)

[Miscellaneous](#)

Environment

[Environmental Confirmations](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SP3725-2>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SP3725-2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SP3725-2

CAX-Online-Generator





last modified:

3/12/2024 

