

FEATURES

- 10mm coloured diffused epoxy lens
- Various AC voltages
- 16 mm chrome bezel
- Longevity and low power consumption

RS PRO Red Indicator, 110 V ac, 14mm Mounting Hole Size, Solder Tab Termination, IP67

RS Stock No.: 204-495



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Brought to you by RS Pro, a high quality range of LED indicators. Each indicator has a compact and durable build, enhanced by their IP67 rating. Making them perfect for both indoor and outdoor harsh environments. Quick and easy installation is a primary feature of these indicators, each unit includes solder lug terminals for convenience. All models are highly reliable and excellent quality.

General Specifications

Light Output Colour	Red		
Lamp Type	LED		
Termination Type	Solder Tab		
Туре	Panel Mount		
Bezel Style	Prominent		
Bezel Colour	Chrome		
Intensity	80mcd		
Type Of Illumination	Fixed Light		
LED Colour	Red		
Viewing Angle	30° to 100°		
Life Expectancy	100000hours		
Applications	Fixed to PCB circuit boards mounted; Switches; Pushbuttons; Used as vehicle indicators		

Electrical Specifications

Voltage Rating	110V ac
Current Rating	6mA
Voltage Tolerance	10%



Mechanical Specifications

Mounting Hole Size	14mm
Length	61mm
Torque	75cNm
Lamp Size	10mm

Operation Environment Specifications

Temperature Rating	-40°C to 85°C	
--------------------	---------------	--

Protection Category

IP Rating	IP67	

Approvals

Compliance/Certifications	EN61340



Indicators



TECHNICAL SPECIFICATIONS			
Voltage	Operating Voltage	Operating Current	
	(Min to Max)	(Typical All Types)	
02 (No Resistor)	1.8 to 3.3VDC	20mA max*	
6VDC	5.4 to 6.6VDC	20mA	
12VDC	10.8 to 13.2VDC	20mA	
24VDC	21.6 to 26.4VDC	20mA	
28VDC	25.2 to 30.8VDC	20mA	
110VAC	99 to 121VAC	6mA	
220VAC	207 to 253VAC	3mA	

For DC Supply versions: gold colored contact is Anode (+)

Max Reverse Voltage: 5V		
Viewing Angle: 30–100° (dependant on model)		
Life Expectancy: 100,000 hours		
Temperature Range: -40 to +85°C (operating & storage)		
Torque: 75cNm		
PANEL CUTOUT 17.00 [0.660] AF 17.00 [0.660] AF M14 x 1,0 THREAD		

Standard LED Intensity	Prominent and Recessed	Flush	Forward Voltage
HE Red	80mcd	10mcd	2.0V
Green	60mcd	5mcd	2.2V
Yellow	50mcd	4mcd	2.1V
Blue	540mcd	100mcd	3.3V
White	1000mcd	150mcd	3.3V
Orange	80mcd	200mcd	2.0V
Bi-color (Typical) (Red/Green)	15/15mcd	14/10mcd	2.0V/2.2V
Tri-color (Typical) (Red/Green/Yellow)	60/50/50mcd	15/10/30mcd	2.0V/2.2V/2.1V
Bi-color - The color	is changed by reversing the po	plarity of the supply vol	tage.
Tri-color - The indicator ha	as red and green LEDs, when b	oth connected yellow	is produced.
Super Bright LED	Prominent and Recessed	Flush	Forward Voltage
HE Red	17,000mcd	2,000mcd	2.2V
Green	11,000mcd	680mcd	3.5V
Yellow	4,000mcd	350mcd	2.3V
Blue	2,500mcd	250mcd	3.3V
White	4,400mcd	250mcd	3.3V
Orange	2800mcd	300mcd	2.1V
Hyper Bright LED	Prominent and Recessed	Flush	Forward Voltage
HE Red	2,800mcd	800mcd	2.1V
Green	2,200mcd	250mcd	3.2V
Yellow	1,300mcd	250mcd	2.0V
Orange	850mcd	200mcd	2.1V
Luminous ir	ntensity will be reduced with lover	wer operating current.	



PROMINENT BEZEL













