

Product datasheet

Specifications



4 THREADED BARS 400A L1000/ LINERGY BS BB

LVS04163

EAN Code: 3606481870261

Main

Range	Linery
Range of product	Linery
Product or component type	Busbar
product name	Linery BS
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P enclosure
Busbar description	Flat bar
Quantity per set	Set of 4

Complementary

Installation direction	Vertical, operating position: rear
installation description	Cubicle - width 650 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
[Ie] rated operational current	400 A at 35 °C
[Icw] rated short-time withstand current	20 kA (1 s) for 3 supports
[Ipk] rated peak withstand current	55 kA
Busbar cross section	32 x 5 mm
Length	1000 mm
Width	32 mm
Depth	5 mm
Net weight	5.7 kg
Colour	Natural
Type of busbar connection	M6 threaded hole
Connection pitch	Connection each 25 mm

Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of Units in Package 1	1
Package 1 Height	1.600 cm
Package 1 Width	13.200 cm
Package 1 Length	109.300 cm
Package 1 Weight	5.608 kg
Unit Type of Package 2	P12
Number of Units in Package 2	60
Package 2 Height	32.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	348.500 kg

Logistical informations

Country of origin	FR
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	119
Environmental Disclosure	Product Environmental Profile

Use Better


Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
Halogen content performance	Halogen free plastic parts product
PVC free	Yes

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Technical Illustration

Dimensions



- All dimensions are approximate and are in
- Also see technical documentation.