

Eaton 135718

Catalog Number: 135718

Eaton Moeller® series E65 Retroreflective sensing sensor, Sn=3m, 4L, 10-30VDC, dark, NPN, PNP, quad 40, insulated material, line 2m



General specifications

Product Name	Catalog Number
Eaton Moeller® series E65 Retroreflective sensor	135718 EAN 4015081325115
Product Length/Depth	Product Height
139.7 mm	139.7 mm
Product Width	Product Weight
38.1 mm	0.11 kg
Certifications	Catalog Notes
UL Certified by UL for use in Canada UL 508 CSA-C22.2 No. 14 UL Category Control No.: NRKH, NRKH7	Yellow
IEC/EN 60947-5-2 UL File No.: E166051 CE CSA File No.: UL report applies to both US and Canada	

Product specifications

Type

Optical sensors

Features

Polarized light

Electric connection type

Cable

Enclosure material

Plastic

Enclosure type

Cuboid

Operating mode

Switching principle: Dark switching

Explosion safety category for dust

None

Explosion safety category for gas

None

Functions

For combination with reflector

Short-circuit protection

Protection against wire breakage

Reflected-light beam

Protection against polarity reversal

Voltage type

DC

Connection type

2 m connection cable

4-wire

Light type

Other

Degree of protection

IP68

NEMA 6P, 13

Interface type

Other

LED indicator

Status indication of Switching state: Red LED

Status indication of Operating voltage: Green LED

Resources

Catalogs

Product Range Catalog Sensors – products, basic information, applications

Declarations of conformity

DA-DC-00004652.pdf

DA-DC-00004657.pdf

Drawings

eaton-proximity-switches-dimensions.eps

eaton-proximity-switches-dimensions-012.eps

eaton-proximity-switches-dimensions-011.eps

eaton-proximity-switches-3d-drawing.eps

Installation instructions

IL05305004Z

mCAD model

DA-CS-90_28290_006

DA-CD-90_28290_006

Switch function type

Other

Load current

Max. 100 mA (I_e)

Laser protection class

None

Shock resistance

50 g, Mechanical, Shock duration 10 ms

Optical surface material

Plastic

Output current (mA) - max

100 mA

Output current at protected output - max

0 mA

Rated control supply voltage (U_s) at AC, 50 Hz - max

0 V

Rated control supply voltage (U_s) at AC, 50 Hz - min

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - max

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - min

0 V

Rated control supply voltage (U_s) at DC - max

30 V

Rated control supply voltage (U_s) at DC - min

10 V

Rated switching distance (S_n)

3000 mm

Reflector distance - min

0 mm

Sensor height

43 mm

Sensor length

41 mm

Switching distance - max

0 mm

Switching voltage of OSSD at state high

30 V

Transmission range of the safety field

0 m

Voltage rating - max

30 V

Safety type (IEC 61496-1)

1

Switching frequency

500 Hz

Sensing mode

Dark switching

Switching output type

PNP

Sensor material

Insulated material

Wavelength of the sensor

660 nm

Width sensor

33 mm

Product category

E65 SM Series

Response time

1 ms

Ambient operating temperature - max

55 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

-25 °C

Diameter sensor

0 mm

Light dot size

0 mm²

Number of contact energized outputs with signalling function

0

Number of outputs (protected contact energized)

0

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

2

Operating temperature - max

55 °C

Operating temperature - min

-25 °C

Operational current (Ib) in the switched state at 24 V DC

20 A

Adjustment type

Other



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia