



18V Combi Drill Brushless LXT® DHP490

Model DHP490 is a Combi Drill powered by an 18V LXT Li-ion battery.

This model ensures sufficient torque by adopting a Brushless Motor is lightweight and compact, easy to handle even in narrow spaces. Features and Benefits: Max.torque of 65Nm, Mechanical 2 speed, Electric brake, Variable speed control by trigger



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 500 / 1900 min ⁻¹
Max. fastening torque Hard/Soft	50 / 27 Nm
Max Torque	65 Nm
Torque setting	20
Impacts per Minute (IPM)	0 - 7500 / 28500 min ⁻¹
Max. Drilling Diameter in Wood	38 mm
Max. Drilling Diameter in Masonry	13 mm
Max. Drilling Diameter in Steel	13 mm
Drilling Capacity Wood (Auger Bit)	38 mm
Drilling Capacity Wood (Self-feed bit)	38 mm
Drilling Capacity Flat bit	40 mm
Drilling Capacity Hole Saw	51 mm

User benefits

- Keyless chuck for easy bit installation and removal
- Mechanical 2-speed gearing; High speed mode for speedy drilling in light duty applications; Low speed mode for heavy duty applications requiring high torque
- Built-in LED light with pre-glow and afterglow functions illuminates the work area
- Variable speed trigger allows operator to adjust speed based on materials or application
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing