

PRODUCT-DETAILS

GSB312

2-PC INNER SLV CONN PUR I.D. 0.312



General Information

Extended Product Type	GSB312
Product ID	7TAI029070R0032
EAN	5414363113867
Catalog Description	2-PC INNER SLV CONN PUR I.D. 0.312
Long Description	Two Piece Inner Sleeve Connector for Hexagonal Range, Length 7.9mm, Inner Diameter 7.92mm, Outer Diameter 9.20mm, Color Purple, Hard Bronze, Tin Plated

Ordering

EAN	5414363113867
UPC	786210813264

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	4.5 in 114 mm
Package Level 1 Height	3 in 76 mm
Package Level 1 Depth / Length	5 in 127 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	10.7 in 272 mm

Package Level 2 Height	3.5 in 89 mm
Package Level 2 Depth / Length	23.9 in 607 mm

Additional Information

Brand / Label	Sta-Kon
Color	Purple
Effective Date	19680516
Material	Hard Bronze
Number of Batteries	0
Product Name	STA-KON AND CATAMOUNT TERMINAL
Product Type	Two-Piece Inner Sleeve Connector
Special Functions	Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Inner sleeve for the Hexagonal Range (the corresponding outer sleeve is crimped with a hand tool and the result is a hexagonal-shaped crimp), for grounding shielded and coaxial cables. The sleeves are color coded according to their size. Millions of installations in communications, aerospace, electronic, telephone, radio and TV applications.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	GSB312
Instructions and Manuals	GSB312
RoHS Information	9AKK107992A4006

Classifications

ETIM 6	EC002650 - Connection for screened wires
ETIM 7	EC002650 - Connection for screened wires
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

