



2600 series | Openable from both sides along the inner radius | Inner height: 35mm

2600.10.100.0



2600 series | Openable from both sides along the inner radius | Inner height: 35mm

- Inner height hi: 35mm
- Inner width Bi: 50 - 175mm
- Bend radii R: 63 - 250mm
- Pitch: 56mm
- Openable from both sides (from left and right) along the inner radius
- High strength paired with quieter motion
- Easy and versatile assembly
- Long cable life

Outer height Ha	50 mm
Inner height [Hi]	35 mm
Inner width [Bi]	100 mm
Max. cable diameter	32 mm
Outer width [Ba]	116 mm

Product description

Introducing the 2600 series from the E2/000 system, designed for versatility and durability. This innovative system opens from both sides along the inner radius, featuring an inner height of 35 mm. Enjoy easy assembly and a robust design that ensures quieter motion and extended cable life. With a double stop system for large unsupported lengths and modular interior separation, the 2600 series is perfect for a variety of applications. Elevate your projects with this reliable and efficient solution.

Thermal properties

Temperature e-chain®	-40°C to +120°C
----------------------	-----------------

Dynamic properties

v max. unsupported (speed)	20 m/s
v max. gliding (speed)	10 m/s



Dimensions

Inner height [Hi]	35 mm
Inner width [Bi]	100 mm
Outer height Ha	50 mm
Outer width [Ba]	116 mm
Bend radius [R]	100 mm
Pitch	56 mm
Chain links per metre	18
Max. cable diameter	32 mm
H	250 mm
D	209 mm
K	430 mm
H2	166 mm
D2	395 mm
K2	616 mm
Velocity FLG unsupported max.	20 m/s
Acceleration FLG max.	200 m/s²
Maximum unsupported length	2.75 m
Maximum long travel	120 m


General properties

Opening principle	Openable along inner radius
Maximum fill weight	8 kg/m
Colour	black
Material	igumid G LW
Energy chain system	E2/000
Shipping weight (kg or kg/m)	1.36485
CO2 equivalent per piece	0.459 kg

Certificates and standards



Additional information and diagrams



The unsupported length depends on fill weight

X axis: unsupported length in m FLB/FLG

Y axis: fill weight in kg/m

Lower scale: travel S in m

FLB = unsupported with permissible sag


FLG = unsupported with straight upper run

Reference example A:

fill weight = 1.5 [kg/m]

unsupported length FLB = 2.2 m

travel = 4.4 m



A = Moving end, B = Fixed end

Pitch: 56mm

Chain links per m: 18




Travel: S

Chain length = $\frac{S}{2} + KK$ = Surcharge for bending radius for e-chain length calculation in mm

Note: Chain length for the e-chain links is rounded up, as there are no half links.





Mounting brackets polymer - pivoting





Part number	with tiewrap plates	Mounting type	Alignment (mounting bracket)
2610.34PZ.A1	No	A1	pivoting
2610.34PZ.A2	No	A2	pivoting
2610.34PZ.A3	No	A3	pivoting
2610.34PZ.A4	No	A4	pivoting
2610.34PZB.A1	Yes	A1	pivoting
2610.34PZB.A2	Yes	A2	pivoting
2610.34PZB.A3	Yes	A3	pivoting
2610.34PZB.A4	Yes	A4	pivoting
2610.34PZBK1.A1	Yes	A1	pivoting
2610.34PZBK1.A2	Yes	A2	pivoting
2610.34PZBK1.A3	Yes	A3	pivoting
2610.34PZBK1.A4	Yes	A4	pivoting

Mounting type





Mounting brackets polymer - fixed




Part number	with tiewrap plates	Mounting type	Alignment (mounting bracket)
2610.12PZ.A1	No	A1	fixed
2610.12PZ.A2	No	A2	fixed
2610.12PZ.A3	No	A3	fixed
2610.12PZ.A4	No	A4	fixed
2610.12PZB.A1	Yes	A1	fixed
2610.12PZB.A2	Yes	A2	fixed
2610.12PZB.A3	Yes	A3	fixed
2610.12PZB.A4	Yes	A4	fixed
2610.12PZBK1.A1	Yes	A1	fixed
2610.12PZBK1.A2	Yes	A2	fixed
2610.12PZBK1.A3	Yes	A3	fixed
2610.12PZBK1.A4	Yes	A4	fixed

Mounting type





Mounting brackets KMA - pivoting




Part number	with C-profile	Mounting type	Alignment (mounting bracket)
26001.10.12.A	No	A	pivoting
26001.10.12.C.A1	Yes	A1	pivoting
26001.10.12.C.A2	Yes	A2	pivoting
26001.10.12.C.A3	Yes	A3	pivoting
26001.10.12.C.A4	Yes	A4	pivoting
26001.10.12.C2.A	Yes	C2	pivoting

Mounting type




Mounting brackets KMA - fixed





Part number	with C-profile	Mounting type	Alignment (mounting bracket)
26101.10.12.A	No	A	fixed
26101.10.12.C.A1	Yes	A1	fixed
26101.10.12.C.A2	Yes	A2	fixed
26101.10.12.C.A3	Yes	A3	fixed
26101.10.12.C.A4	Yes	A4	fixed
26101.10.12.C2.A	Yes	C2	fixed

Mounting type





Mounting brackets steel - fixed



Part number	Variant (mounting bracket)
260.12	zinc-coated





Seperators



Standard separator, wide base, unassembled

Standard - for any application. Separator with a wide base for maximum holding force.

Part number	Mounted
35.1	No





Lean separator, unassembled

Lean separators. For quick fitting of shelves in several layers.

Part number	Mounted
35.12	No







Separator, narrow top, unassembled

Even faster cable installation. Wide on one side for high holding force, narrow on opposite side for easy cable fitting.

Part number	Mounted
35.2	No




Separator, narrow, unassembled

For a large number of thin cables. Separator with a narrow base for a large number of small cables side by side. Space-saving in energy chains.

Part number	Mounted
35.3	No







Separator, asymmetrical, unassembled

For e.g. Side-mounted applications. Asymmetrical separator, for defined gap distance. No additional spacers required.

Part number	Mounted
35.4	No



Notch separator, unassembled

Locks securely in preset increments. Notch separator for exact positioning. Recommended for side-mounted applications.

Part number	Mounted
35.5	No



Separator, unassembled

Separator, unassembled

Part number	Mounted
260	No

Separator, unassembled

Separator, unassembled

Part number	Mounted
260.24	No



Middle plate, unassembled

Middle plate, unassembled

Part number	Mounted
262	No

Height slot separator, unassembled

Height slot separator, unassembled

Part number	Mounted
266	No



Separator, slotted, unassembled

Separator, slotted, unassembled

Part number	Mounted
268	No



Height slot separator, open, unassembled

Height slot separator, open, unassembled

Part number	Mounted
276	No



Shelves



Part number	Width	Mounted
220.100	100 mm	No
220.50	50 mm	No
220.65	65 mm	No
220.75	75 mm	No
220.90	89 mm	No
2200.18	19.2 mm	No
2200.23	24.2 mm	No
2200.28	29.2 mm	No
2200.33	34.2 mm	No
2200.38	39.2 mm	No
2200.42	43.2 mm	No
2200.43	44.2 mm	No
2200.48	49.2 mm	No
2200.58	59.2 mm	No
2200.65	66.2 mm	No
2200.68	69.2 mm	No
2200.73	74.2 mm	No
2200.88	89.2 mm	No
2200.99	99.2 mm	No
3200.025	25 mm	No
3200.037	37 mm	No
3200.040	40 mm	No
3200.050	50 mm	No
3200.068	68 mm	No
3200.075	75 mm	No
3200.087	87 mm	No
3200.090	90 mm	No
3200.100	100 mm	No