

# Swivel Stem Castor, grey rubber 63mm, 40kg

## Swivel Stem Castor

PRODUCT

Article number

DP2FA063-325L10

DP2FD063-325L10



### Product Details

Castor assembly : Pressed steel, zinc plated housing, with threaded stem fitting.

Swivel : Swivel on two rows of balls.

Double-acting lock on wheel and pivot. Grey nylon pedal.

Rim : Grey Polypropylene.

Tread : Grey synthetic Rubber. Non-marking.

Hub : Plain bearing.

Specifications	Threaded Stem	
Wheel Diameter - ØD ± 1%	63 mm	
Hub Type	Plain bore	
Hub Length	24 mm ±1	
Width of Tread	22mm ±1	
Width of Tread-on floor	22 mm ±1	
Overall Height	90 mm	
Offset	25 mm	
Fitted Stem Diameter	10 mm	
Fitted stem Height	25 mm	
Hardness of tread A ±3	A 80° Shore	
Load capacity	40 Kg	
Temperature	-5 / +50 °C	
Weight	Swivel = 0,3 kg	Swivel+brake = 0,35 kg

TECHNICAL DATA

### Applications :

Medium-weight appliances and furniture.

Non-marking. Materials handling on indoor or warehouse floors.

Quiet.

Easy to assemble with the crimped stem.

Stem is united to the housing.