
Technical sheet

BTC40BATFLEX

Swing door suitable for Ø 40 mm barrier

This swing gate is designed to fit barriers with a diameter of 40 mm, offering a simple, robust and flexible access solution. It is designed for industrial or logistics environments requiring a pedestrian opening in an existing barrier structure. Thanks to its AISI 316 stainless steel hinges and stainless steel fasteners, it guarantees excellent corrosion resistance and long-lasting durability.













Customs code	7326909890
EAN	3321360117083

Color : Yellow

Material : Galvanized steel

Specifications :

- Highly versatile two-way swing gate.
- Fits any barrier or post with a diameter of 40 mm.
- Secured using 2 screw-on clamps with foam protection.
- Fitted with a removable stop to lock the gate if required.
- Includes a 250 x 160 mm plate.
- Do not install in environments with salt or hydrocarbons.

Length (mm)	Height (mm)	Net weight (kg)
867	242	4,50

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France

Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com