

## Metrology-control case 10 tools



### Description:

- Including:
- 805.M: caliper 1/50 mm (capacity 200 mm).
- 806.C25: micrometer 1/100 mm (capacity: 25 mm).
- 806C.50: micrometer 1/100 mm (capacity: 25 - 50 mm).
- 811: depth gauge 1/50 mm (capacity: 160 mm), fine adjustment by return screw.
- 818B.15: simple square 150 mm (accuracy class 1).
- 819B.15: flanged square 150 mm (accuracy class 1).
- 1901.05: straight scriber 150 mm.
- 236: carbide scriber.
- DELA.1051.300: stainless rule 300 mm.
- 256.4: punch.
- Supplied in case (L. x D. x H.): 410 x 280 x 40 mm.

	Depth [mm]	Length L [mm]	Height H [mm]	Weight [Kg]
809.J3	280.0	410.0	40.0	3.6