



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **11**

Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	11
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
Dielectric Withstanding Voltage (Max)	600 V
Insulation Resistance	5000 MΩ

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Layout	Inline
Contact Retention Within Housing	With
Contact Base Material	Phosphor Bronze



Contact Type	Socket
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp, Insulation Displacement (IDC)
------------------------------------	--------------------------------------

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Strain Relief	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Flame-Retardant Thermoplastic
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Connector Height	2.49 mm[.098 in]
Connector Length	2.79 mm[1.098 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-104480-2
SHORT POINT CONT 15 DPLX
STMPD LF

TE Part # 1-104480-3
SHORT POINT CONT 30 DPLX
STMPD LF

TE Part # 1-104481-0
SHORT POINT CONT 15 DPLX
STMPD LF


TE Part # 104479-9
SHORT POINT CONT 15 DPLX
STMPD LF

TE Part # 1-104479-0
SHORT POINT CONT 30 DPLX
STMPD LF

TE Part # 1-104481-1
SHORT POINT CONT 30 DPLX
STMPD LF

TE Part # 104479-8
SHORT POINT CONT PLTD SN

Also in the Series | AMPMODU MTE




Board-to-Board Headers & Receptacles(24)



Connector Caps & Covers(18)




Connector Contacts(27)



Connector Hardware(1)




Insertion & Extraction Tools(1)



PCB Headers & Receptacles(444)



Wire-to-Board Connector Assemblies & Housings(298)



Wire-to-Board Headers & Receptacles (420)

Customers Also Bought



TE Part #2132781-4
04P EP-II HOUSING, NATURAL



TE Part #4-643813-1
11P MTA100 CONN ASSY POL RIB



TE Part #640251-6
06P SL156 HSG W/O LCK RAMP




TE Part #5748678-1
2 PC PLST CBL CLMP KIT




TE Part #1-52929-0
TERMINAL, PIDG SPR SPD 22-16 6



TE Part #1744201-1
EP-II CONTACT LANCELESS, 20-16



TE Part #111620-1
2MM KEYING PLUG, COMB OF 10



TE Part #1-640550-1
11P MTA100 COVER



TE Part #5-747904-2
9 Plug Solder Cup, Gold Flash,



TE Part #5-747905-5
9 Rcpt Solder Cup, 30 gold, Ro

Documents



Product Drawings

11 MTE RCPT HSG SR PLAIN .100

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1-103688-0_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-103688-0_K.3d_igs.zip

English

Customer View Model

ENG_CVM_1-103688-0_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP MODU MTE Section of Catalog 1307819

English

AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT

English

AMPMODU MTE INTERCONNECT SYSTEM

English

Product Specifications

Application Specification

English