



Relays & Contactors > Relay Accessories



Body Material: **Stainless Steel**
Relay Accessory Type: **Accessory, Hold-Down Spring**

Features

Product Type Features

Relay Accessory Type	Accessory, Hold-Down Spring
----------------------	-----------------------------

Body Features

Body Material	Stainless Steel
---------------	-----------------

Other

Relays Comment	Use with R10S (super sensitive relay).
----------------	--

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1393143-2 27E129=SOCKET,R10,16,PC,PHEN	 TE Part # 2-1393143-5 27E213=SOCKET,R10,16,PC,PHEN	 TE Part # 5-1393143-1 27E637=SOCKET,R10,4POLE,PCB,.210	 TE Part # 1-1393143-7 27E163=SOCKET,R10,16,SLG,PHE
 TE Part # 1393143-9 27E126=SOCKET,R10,16,SLG,PHE	 TE Part # 2-1393143-2 27E194=SOCKET,R10,16,PC,PHEN	 TE Part # 4-1393143-8 27E629=SOCKET,R10,4POLE,PCB,.180	

Also in the Series | Potter & Brumfield R10

 AC Relays(9)	 DC Relays(96)	 Electromechanical Relays(105)	 General Purpose Signal Relays(105)
 PCB Headers & Receptacles(1)	 Plug-In Relays(77)	 Relay Accessories(27)	



Customers Also Bought

TE Part #3-1617108-6
PRMAPD-26X = PRMAD COTS TO-5 R

TE Part #CAT-104MTA-PVUNH
PCB Header: Polyester, Vertical, Unshrouded, No Mating Alignment

TE Part #86402-1
20 MODIV HSG SR MRKD .125CL

TE Part #7-1423164-8
7022VCM=RLY,STD,OFF,2P,32VDC,

TE Part #CW4630-000
R85049/90-23N03

TE Part #YDIV43E13-04SNC009
RECP ASSY

TE Part #3-6437128-5
FSN-1.85C-20

TE Part #4-1393143-2
27E447=SOCKET,R10,4POLE,FLG-MNT,SOLDER

TE Part #3-1617086-0
3SBM5004V2 = RELAY

Documents

- CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1393159-5_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1393159-5_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1393159-5_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

- Datasheets & Catalog Pages

R10 Sockets & Accessories

English



[Product Specifications](#)
[Definitions](#) [General Purpose Relays](#)
[English](#)