

# G-INS-M16-T68N-NNES-S - Cable gland



1424526

<https://www.phoenixcontact.com/gb/products/1424526>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: Brass, nickel-plated, application: Standard, external cable diameter 4 mm ... 8 mm, shielding: no, connecting thread: M16 x 1.5, color: silver-colored, with O-ring

## Commercial data

Item number	1424526
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF7DAX
Product key	AF7DAX
Catalog page	Page 688 (C-2-2019)
GTIN	4055626374314
Weight per piece (including packing)	20.9 g
Weight per piece (excluding packing)	19.94 g
Customs tariff number	74198090
Country of origin	TR

# G-INS-M16-T68N-NNES-S - Cable gland



1424526

<https://www.phoenixcontact.com/gb/products/1424526>

## Technical data

### Mounting

Assembly note	1) Mount screw connection support in the housing using the correct torque 2) Insert cable 3) Tighten union nut using the correct torque
---------------	---


### Product properties

Product type	Cable screw gland
Application	Standard
No. of conductors	1
Manufacturer	BIMED
Manufacturer Designation	BMBC-01
Shielded	no
Execution of the strain relief	A

### Characteristics

Category of shock impact	6
Design, Strain relief	A

### Dimensions

Dimensional drawing	
Length	30 mm
Length of the connecting thread	7 mm
Hole diameter	16.1 mm ... 16.3 mm
Wrench size, union nut	17 mm
Wrench size, support	18 mm
Hexagon angular dimension	22 mm
Thread type connection side	M16 x 1.5
Thread pitch	1.5 mm

### Connection data

Tightening torque	6.5 Nm $\pm$ 0.5 Nm (Cap nut)
	4 Nm (Support sleeve)

### Material specifications

Color	brass color
Material Compression ring	PA 6
Seal material O-ring	Perbunan
Seal material Cable seal	CR

# G-INS-M16-T68N-NNES-S - Cable gland



1424526

<https://www.phoenixcontact.com/gb/products/1424526>

Material for screw connection	Brass, nickel-plated
-------------------------------	----------------------

## Cable/line

External cable diameter Cable 1	4 mm ... 8 mm
External cable diameter	4 mm ... 8 mm (for UL 514 B)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66
	IP68 (5 bar, 30 min.)
	IP69 (DIN EN 60529 / IEC 60529)
Ambient temperature (operation)	-40 °C ... 100 °C (static)


# G-INS-M16-T68N-NNES-S - Cable gland

1424526

<https://www.phoenixcontact.com/gb/products/1424526>



## Drawings



Dimensional drawing


# G-INS-M16-T68N-NNES-S - Cable gland



1424526

<https://www.phoenixcontact.com/gb/products/1424526>

## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1424526>

### DNV

Approval ID: TAE00003WY



### cUL Recognized

Approval ID: E199260



### UL Recognized

Approval ID: E199260

# G-INS-M16-T68N-NNES-S - Cable gland



1424526

<https://www.phoenixcontact.com/gb/products/1424526>

## Classifications

### ECLASS

ECLASS-13.0	27140801
-------------	----------

### ETIM

ETIM 9.0	EC000441
----------	----------

### UNSPSC

UNSPSC 21.0	39121300
-------------	----------

# G-INS-M16-T68N-NNES-S - Cable gland



1424526

<https://www.phoenixcontact.com/gb/products/1424526>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d257da9b-9731-4556-a5a3-cfb7023a8d0a

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)