


Product Data Sheet

MaxiFlex® Ultimate™ with AD-APT® 42-875

Colour – Coating	Black
Colour – Liner	Grey
Design	3/4 coated knitwrist
Coating	NBR (Nitrile Butadiene Rubber)
Coating texture	Micro-Foam for Controlled Grip
Liner	Nylon, Spandex
Palm thickness	1.00 mm



Dimensions

Size Range	Size 5 (XXS)	Size 6 (XS)	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)	Size 12 (XXXL)
Total glove length (+/-10 mm)	185	195	205	220	230	235	240	245
Wrist length (mm)	58	63	64	65	70	70	70	75
Wrist width (mm)	67	70	70	75	77	77	78	80
Palm width (+/-3 mm)	78	85	88	90	98	102	104	106
Over lock colour	Purple	Blue	Red	Orange	White	Yellow	Black	Grey

EN test Results

Test	Notified Body	Result/Pass
EN ISO 21420: 2020	TÜV Rheinland	Yes
EN 388: 2016 + A1: 2018	TÜV Rheinland	4131A



Product Data Sheet

MaxiFlex® Ultimate™ with AD-APT® 42-875

Typical Performance Values

EN ISO 21420 Dexterity	Level 5
EN 388:2016 + A1:2018 A. Abrasion Resistance	> 8000 Cycles
EN 388:2016 + A1:2018 B. Cut Resistance	> 1.2 index
EN 388:2016 + A1:2018 C. Tear Resistance	> 50 newtons
EN 388:2016 + A1:2018 D. Puncture Resistance	> 20 newtons
EN 388:2016 + A1:2018 E. Cut Resistance ISO	≥ 2 Newton

HandCare®

Skin Health Alliance Dermatologically Accredited	Yes
REACH compliant	Yes
Standard 100 by OEKO-TEX® (08.BH.57867)	Certified
Washable	60°
Sanitized®	Yes



Special features

AD-APT®	Yes
Silicone free	Yes



Product Data Sheet

MaxiFlex® Ultimate™ with AD-APT® 42-875

Packaging

Pairs per poly bag	12
Poly bags per carton	12
Carton count	144
Carton dimensions (mm)	500 x 295 x 270

Weight

Size Range	Size 5 (XXS)	Size 6 (XS)	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)	Size 12 (XXXL)
Glove weight / Pair (+/-6 gram)	30	32	36	40	44	48	50	52
Gross Weight (Kg)	5.3	5.6	6.2	7	7.3	7.9	8.2	8.5
Carton Weight (Kg)	1	1	1	1	1	1	1	1
Net Weight (Kg)	4.3	4.6	5.2	6	6.3	6.9	7.2	7.5

Issue date: 27.07.2020

