



HANDLE FOR EASY MOVEMENT



360° ROTATION ON VERTICAL AXIS



3 SETTINGS FOR VARIABLE FAN SPEED



360° ROTATION ON HORIZONTAL AXIS



720° ORBITAL AIR CIRCULATION COVERAGE

ITEM. 05635

SIP 20" HEAVY-DUTY ORBITAL FLOOR FAN

MULTI-DIRECTIONAL ORBITAL FAN FOR POWERFUL INDOOR AIR CIRCULATION

PRODUCT OVERVIEW

The **SIP 20" Heavy-Duty Orbital Floor Fan** delivers powerful multi-directional airflow to help cool spaces and circulate air in a variety of indoor environments. Mounted at four point on a steel tube frame, this heavy-duty 3-blade fan can be rotated and fixed between 720° on both its horizontal and vertical axis. This creates an orbital effect which maximises airflow coverage.

Fans are essential in helping to provide improved air quality to indoor spaces.

FEATURES & BENEFITS

✓ POWERFUL AIRFLOW

A heavy-duty 3-blade fan is powered from a 120w motor to deliver powerful and consistent airflow coverage.

✓ VARIABLE SPEED SETTINGS

3 settings for variable fan speed:

- **Low:** 900rpm
- **Medium:** 1100rpm
- **High:** 1300rpm

✓ ORBITAL AIRFLOW FUNCTION

The manually adjustable fan head can rotate 360° on its horizontal axis and 360° on its vertical axis to create 720° coverage of air circulation. The orbital effect created maximises airflow coverage for greater ventilation.

THIS PRODUCT COMES WITH AN SIP 2-YEAR SILVER WARRANTY*

FIND OUT MORE AT SIP-GROUP.COM/WARRANTY



ITEM. 05635

SIP 20" HEAVY-DUTY ORBITAL FLOOR FAN

FEATURES & BENEFITS CONT.

✔ OUTSTANDING MOBILITY

A sturdy and compact design allows the fan to be easily moved between locations for use.

✔ ENHANCED SAFETY FEATURES

Fan blades are fully enclosed with solid mesh steel guarding for greater user safety.

A robust and balanced steel frame maintains fan stability when in use.

APPLICATIONS & USES

**DELIVERS POWERFUL VARIABLE SPEED
AIR CIRCULATION TO INDOOR SPACES**

**PERFECT FOR INDUSTRIAL, COMMERCIAL
& AGRICULTURAL WORKSHOP AREAS**

ITEM NO.	05635		
INPUT SUPPLY	230v (13A)		
MOTOR POWER	120w (0.16hp)		
POWER CABLE	180cm		
FAN DIAMETER	Ø 20" (508mm)		
SPEED SETTINGS	3 speed settings		
	Low	Medium	High
	900rpm	1100rpm	1300rpm
NOISE LEVEL	68dB(A)		
NET WEIGHT	6.4kg		
GROSS WEIGHT	7.8kg		
PRODUCT DIMENSIONS	695(H) x 665(W) x 258mm(D)		
PACKAGED DIMENSIONS	765(H) x 710(W) x 270mm(D)		