



T-nut






- ▶ Standard element for a secure and conductive connection
- ▶ End stop for correct positioning in the profile slot
- ▶ Stainless steel T-nut, e.g. for outdoor or cleanroom applications
- ▶ Profile finishing: not required


Technical data (p. 19-5)


Accessories:
insulating cap (p. 3-5)









Slot	
6	1700 N


T-nut, 6 mm slot	Slot	M	ESD	No.
steel; galvanized	6	M4		100 3 842 523 135
Stainless steel	6	M4		100 3 842 536 599




Slot	
8 (M6)	4000 N









T-nut, 8 mm slot	Slot	M	ESD	No.
steel; galvanized	8	M4		100 3 842 501 751
		M5*		100 3 842 501 752
		M6*		100 3 842 501 753
Stainless steel	8	M4		100 3 842 536 600
		M5		100 3 842 536 601
		M6		100 3 842 536 602

* Suitable for flat top chains. **Caution:** T-nuts have driving torque for safe turning in the base of the slot.



Slot	
10 (M8)	6000 ... 18000 N ¹⁾

¹⁾ Depending on profile (p. 19-5)

T-nut, 10 mm slot	Slot	M	ESD	No.
steel; galvanized	10	M4		100 3 842 530 281
		M5*		100 3 842 530 283
		M6*		100 3 842 530 285
		M8*		100 3 842 530 287
Stainless steel	10	M4		100 3 842 536 606
		M5		100 3 842 536 605
		M6		100 3 842 536 604
		M8		100 3 842 536 603

* Suitable for flat top chains. **Caution:** T-nuts have driving torque for safe turning in the base of the slot.