

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0009501051](#)  
**Status:** **Active**  
**Overview:** SPOX Connector System  
**Description:** 3.96mm Pitch SPOX Crimp Housing, Female, with Friction Ramp, 5 Circuits, Natural

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-5195-006-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Product Specification PS-5195-007-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-5273-003 (PDF)</a>
<a href="#">Product Specification PS-5195-003 (PDF)</a>	<a href="#">Product Specification PS-5273-004 (PDF)</a>
<a href="#">Product Specification PS-5195-005-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">5195</a>
Application	Signal, Wire-to-Board
Overview	<a href="#">SPOX Connector System</a>
Product Name	SPOX
UPC	800753534445

**Physical**

Circuits (maximum)	5
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	1467.100/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Material Info**

Engineering Number	5195-05
--------------------	---------

**Reference - Drawing Numbers**

Product Specification	PS-5195-003, PS-5195-005-001, PS-5195-006-001, PS-5195-007-001, PS-5273-003, PS-5273-004
Sales Drawing	SD-5195-N

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ECHA\_01\_2020 (16 January 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[5195 Series](#)

**Mates With**

[5272](#) , [5273](#) , [5274](#) , [5096](#) , [53405](#) , [5271](#)

**Use With**

[5194](#)