**New Product** 



## ESH2PB, ESH2PC & ESH2PD

Vishay General Semiconductor

# **High Current Density Surface Mount Ultrafast Rectifiers**



DO-220AA (SMP)

| PRIMARY CHARACTERISTICS  |                     |  |  |  |  |
|--------------------------|---------------------|--|--|--|--|
| I <sub>F(AV)</sub> 2.0 A |                     |  |  |  |  |
| V <sub>RRM</sub>         | 100 V, 150 V, 200 V |  |  |  |  |
| t <sub>rr</sub>          | 25 ns               |  |  |  |  |
| $V_F$ at $I_F = 2 A$     | 0.75 V              |  |  |  |  |
| T <sub>J</sub> max.      | 175 °C              |  |  |  |  |

### **TYPICAL APPLICATIONS**

For use in secondary rectification and freewheeling for ultrafast switching speeds of ac-to-ac and dc-to-dc converters in high temperature conditions for both consumer and automotive applications.

## FEATURES

- Very low profile typical height of 1.0 mm
- Ideal for automated placement
- Glass passivated chip junction
- Ultrafast recovery times for high frequency
- · Low forward voltage drop, low power loss
- Low thermal resistance
- Meets MSL level 1 per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
- Compliant to RoHS directive 2002/95/EC and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21
  definition
- Find out more about Vishay's Automotive Grade Product requirements at: www.vishay.com/applications

## **MECHANICAL DATA**

Case: DO-220AA (SMP)

Molding compound meets UL 94 V-0 flammability rating.

Base P/N-M3 - halogen-free and RoHS compliant, commercial grade

Base P/NHM3 - halogen-free and RoHS compliant, automotive grade

**Terminals:** Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 suffix meets JESD 201 class 1A whisker test, HM3 suffix meets JESD 201 class 2 whisker test

Polarity: Color band denotes cathode end

| MAXIMUM RATINGS (T <sub>A</sub> = 25 °C unless otherwise noted)                   |                                   |               |        |        |      |
|---|-----------------------------------|---------------|--------|--------|------|
| PARAMETER   | SYMBOL                            | ESH2PB        | ESH2PC | ESH2PD | UNIT |
| Device marking code   |                                   | P2B           | P2C    | P2D    |      |
| Maximum repetitive peak reverse voltage   | V <sub>RRM</sub>                  | 100           | 150    | 200    | V    |
| Maximum average forward rectified current (fig. 1)                                | I <sub>F(AV)</sub>                | 2.0           |        |        | A    |
| Peak forward surge current 10 ms single half sine-wave superimposed on rated load | I <sub>FSM</sub>                  | 50            |        |        | A    |
| Operating junction and storage temperature range                                  | T <sub>J</sub> , T <sub>STG</sub> | - 55 to + 175 |        |        | °C   |

| <b>ELECTRICAL CHARACTERISTICS</b> (T <sub>A</sub> = 25 °C unless otherwise noted) |   |   |                 |              |              |      |  |
|---|---|---|-----------------|--------------|--------------|------|--|
| PARAMETER   | TEST CONDITIONS   |   | SYMBOL          | TYP.         | MAX.         | UNIT |  |
| Maximum instantaneous forward voltage <sup>(1)</sup>                              | I <sub>F</sub> = 2 A  | T <sub>J</sub> = 25 °C<br>T <sub>J</sub> = 125 °C | V <sub>F</sub>  | 0.90<br>0.75 | 0.98<br>0.82 | V    |  |
| Maximum reverse current <sup>(2)</sup>  | Rated V <sub>R</sub>  | T <sub>J</sub> = 25 °C<br>T <sub>J</sub> = 125 °C | I <sub>R</sub>  | 0.2<br>12.6  | 1.0<br>25    | μΑ   |  |
| Maximum reverse recovery time   | $I_{\rm F} = 0.5 \text{ A}, I_{\rm R} = 1 \text{ A}, I_{\rm rr} = 0.25 \text{ A}$ |   | t <sub>rr</sub> | -            | 25           | ns   |  |

Pb

FREE

AUTOMOTIVE

ROHS COMPLIANT HALOGEN

# ESH2PB, ESH2PC & ESH2PD





| <b>ELECTRICAL CHARACTERISTICS</b> (T <sub>A</sub> = 25 °C unless otherwise noted) |  |   |                 |        |          |      |
|---|--|---|-----------------|--------|----------|------|
| PARAMETER   | TEST CONDITIONS  |   | SYMBOL          | TYP.   | MAX.     | UNIT |
| Typical reverse recovery time   | l <sub>F</sub> = 1.0 A, V <sub>R</sub> = 30 V,<br>dl/dt = 50 A/μs, | T <sub>J</sub> = 25 °C<br>T <sub>J</sub> = 100 °C | t <sub>rr</sub> | -<br>- | 25<br>35 | ns   |
| Typical stored charge   | $I_{rr} = 10 \% I_{RM}$  | T <sub>J</sub> = 100 °C                           | Q <sub>rr</sub> | -      | 10<br>15 | nC   |
| Typical junction capacitance  | 4.0 V, 1 MHz   |   | CJ              | -      | 25       | pF   |

Notes:

 $^{(1)}$  Pulse test: 300  $\mu s$  pulse width, 1 % duty cycle

<sup>(2)</sup> Pulse test: Pulse width  $\leq$  40 ms

| <b>THERMAL CHARACTERISTICS</b> (T <sub>A</sub> = 25 °C unless otherwise noted) |  |        |                |        |      |
|--|--|--------|----------------|--------|------|
| PARAMETER  | SYMBOL   | ESH2PB | ESH2PC         | ESH2PD | UNIT |
| Typical thermal resistance <sup>(1)</sup>                                      | $f R_{	heta JA} \ R_{	heta JL} \ R_{	heta JC}$ |        | 80<br>15<br>22 |        | °C/W |

#### Note:

<sup>(1)</sup> Thermal resistance from junction to ambient and junction to lead mounted on P.C.B. with 6.0 mm x 6.0 mm copper pad areas.  $R_{\theta JL}$  is measured at the terminal of cathode band.  $R_{\theta JC}$  is measured at the top center of the body

| ORDERING INFORMATION (Example) |                 |                        |               |                                    |  |  |  |
|--------------------------------|-----------------|------------------------|---------------|------------------------------------|--|--|--|
| PREFERRED P/N                  | UNIT WEIGHT (g) | PREFERRED PACKAGE CODE | BASE QUANTITY | DELIVERY MODE                      |  |  |  |
| ESH2PB-M3/84A                  | 0.024           | 84A                    | 3000          | 7" diameter plastic tape and reel  |  |  |  |
| ESH2PB-M3/85A                  | 0.024           | 85A                    | 10 000        | 13" diameter plastic tape and reel |  |  |  |
| ESH2PBHM3/84A <sup>(1)</sup>   | 0.024           | 84A                    | 3000          | 7" diameter plastic tape and reel  |  |  |  |
| ESH2PBHM3/85A <sup>(1)</sup>   | 0.024           | 85A                    | 10 000        | 13" diameter plastic tape and reel |  |  |  |

Note:

<sup>(1)</sup> Automotive grade

## **RATINGS AND CHARACTERISTICS CURVES**

(T<sub>A</sub> = 25 °C unless otherwise noted)




Figure 1. Forward Current Derating Curve




Figure 2. Maximum Non-Repetitive Peak Forward Surge Current



1000

100

10

1

0.1

1

Junction Capacitance (pF)



# ESH2PB, ESH2PC & ESH2PD

Vishay General Semiconductor

Π

Reverse Voltage (V)

Figure 5. Typical Junction Capacitance

10

100




Figure 3. Typical Instantaneous Forward Characteristics





Figure 4. Typical Reverse Leakage Characteristics





For technical questions within your region, please contact one of the following: PDD-Americas@vishay.com, PDD-Asia@vishay.com, PDD-Europe@vishay.com



Vishay

# Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.