


SEP8705

AlGaAs Infrared Emitting Diode

FEATURES

- T-1 package
- 15° (nominal) beam angle
- 880 nm wavelength
- Consistent optical properties
- Higher output than GaAs at equivalent drive current
- Mechanically and spectrally matched to SDP8405 phototransistor and SDP8105 photodarlington




DESCRIPTION

The SEP8705 is an aluminum gallium arsenide infrared emitting diode transfer molded in a T-1 smoke gray plastic package. Transfer molding of this device assures superior optical centerline performance compared to other molding processes. These devices typically exhibit 70% greater power intensity compared to GaAs devices at the same forward current. Lead lengths are staggered to provide a simple method of polarity identification.

OUTLINE DIMENSIONS in inches (mm)

Tolerance	3 plc decimals	$\pm 0.005(0.12)$
	2 plc decimals	$\pm 0.020(0.51)$



DIM_101.ds4

© Honeywell Inc.

Honeywell

Honeywell reserves the right to make changes in order to improve design and supply the best products possible.

SEP8705

AlGaAs Infrared Emitting Diode

ELECTRICAL CHARACTERISTICS (25°C unless otherwise noted)

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	TEST CONDITIONS
Irradiance ⁽¹⁾ SEP8705-001 SEP8705-002 SEP8705-003	H	0.54		5.6	mW/cm ²	I _F =20 mA
		1.4				
		2.7		7.8		
Forward Voltage	V _F		1.7		V	I _F =20 mA
Reverse Breakdown Voltage	V _{BR}	3.0			V	I _R =10 µA
Peak Output Wavelength	λ _p	880			nm	
Spectral Bandwidth	Δλ	80			nm	
Spectral Shift With Temperature	Δλ _p /ΔT	0.2			nm/°C	
Beam Angle ⁽²⁾	Ø	15			degr.	I _F =Constant
Radiation Rise And Fall Time	t _r , t _f		0.7		µs	

Notes

1. Measured in mW/cm² into a 0.081(2.05) diameter aperture placed 0.40(10.16) from the lens tip.
2. Beam angle is defined as the total included angle between the half intensity points.

ABSOLUTE MAXIMUM RATINGS


(25°C Free-Air Temperature unless otherwise noted)

Continuous Forward Current	50 mA
Power Dissipation	70 mW ⁽¹⁾
Operating Temperature Range	-40°C to 85°C
Storage Temperature Range	-40°C to 85°C
Soldering Temperature (5 sec)	240°C

Notes

1. Derate linearly from 25°C free-air temperature at the rate of 0.18 mW/°C.

SCHEMATIC



Honeywell reserves the right to make changes in order to improve design and supply the best products possible.

Honeywell

© Honeywell Inc.

SEP8705

AlGaAs Infrared Emitting Diode

Fig. 1 Radiant Intensity vs Angular Displacement




Fig. 3 Forward Voltage vs Forward Current




Fig. 5 Spectral Bandwidth




Fig. 2 Radiant Intensity vs Forward Current




Fig. 4 Forward Voltage vs Temperature





Fig. 6 Coupling Characteristics with SDP8405




SEP8705

AlGaAs Infrared Emitting Diode

Fig. 7 Relative Power Output vs
Free Air Temperature

gra_130.ds4



All Performance Curves Show Typical Values

Honeywell reserves the right to make
changes in order to improve design and
supply the best products possible.

Honeywell

© Honeywell Inc.