

# guided drive DFM-63-200-P-A-GF



Part number: 170884

★ Core product range

FESTO

With integrated guide.

The proximity switch, type SMTSO-8E, can be used with this product with stroke lengths equal to or greater than 50 mm. The corresponding mounting kit, type SMB-8E, is mounted inwardly or outwardly.



## Data sheet

| Feature   | Value   |
|---|---|
| Centre of gravity distance from working load to yoke plate          | 50 mm   |
| Stroke  | 200 mm  |
| Piston diameter   | 63 mm   |
| Operating mode of drive unit  | Yoke  |
| Cushioning  | P: Flexible cushioning rings/plates at both ends                            |
| Assembly position   | Any   |
| Guide   | Plain-bearing guide   |
| Design structure  | Guide   |
| Position detection  | For proximity sensor  |
| Operating pressure  | 1 ... 10 bar  |
| Max. speed  | 0.6 m/s   |
| Mode of operation   | double-acting   |
| Operating medium  | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium                                  | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC                             | 1 - Low corrosion stress  |
| Ambient temperature   | -20 ... 80 °C   |
| Impact energy in end positions                                      | 1.3 Nm  |
| Max. permissible torque load Mx as a function of the stroke         | 10.7 Nm   |
| Max. useful load as a function of the stroke at defined distance xs | 174 N   |
| Theoretical force at 6 bar, return stroke                           | 1,750 N   |
| Theoretical force at 6 bar, advance stroke                          | 1,870 N   |
| Moving mass   | 4,375 g   |
| Product weight  | 10,142 g  |
| alternative connections   | See product drawing   |
| Pneumatic connection  | G1/4  |
| Materials note  | Conforms to RoHS  |
| Material cover  | Wrought Aluminium alloy   |
| Material seals  | NBR   |
| Material housing  | Wrought Aluminium alloy   |
| Material piston rod   | High alloy steel, non-corrosive   |