


## Switching element - New Version

704.917.4-1



<https://www.eao.com/component/704.917.4-1/en/...>

Your product:



# 704.917.4-1

## Switching element - New Version

**ELECTRICAL CHARACTERISTICS**

**Switching voltage and switching current:**

|                             |                   |       |
|-----------------------------|-------------------|-------|
| as per DIN EN IEC 60947-5-1 |                   |       |
| voltage                     | DC13              | AC15  |
| 24 V                        | 4.0 A             | 8.0 A |
| 60 V                        | 1.5 A             | 8.0 A |
| 110 V                       | 1.0 A             |       |
| 120 V                       |                   | 8.0 A |
| 230 V                       | 0.4 A             | 7.0 A |
| 400 V                       | 0.2 A             | 5.0 A |
| 500 V                       | 0.15 A            | 4.0 A |
| as per UL 60947-5-1         |                   |       |
| voltage                     | power             |       |
| 24 VDC                      | 4.0 A, Pilot duty |       |
| 60 VDC                      | 1.5 A, Pilot duty |       |
| 120 VDC                     | 1.0 A, Pilot duty |       |
| 240 VDC                     | 0.4 A, Pilot duty |       |
| 415 VDC                     | 0.2 A, Pilot duty |       |
| 480 VDC                     | 0.14A, Pilot duty |       |
| 120 VAC                     | 8.0 A, Pilot duty |       |
| 240 VAC                     | 7.0 A, Pilot duty |       |
| 415 VAC                     | 5.0 A, Pilot duty |       |
| 480 VAC                     | 4.0 A, Pilot duty |       |

**Contacts:** 2 NC

**Rated impulse withstand voltage Uimp:** 4 kV

**Rated insulation voltage Ui:** 500 V

|                                              |                      |        |
|----------------------------------------------|----------------------|--------|
| <b>Recommended minimum operational data:</b> | Gold-silver contacts |        |
|                                              | Voltage              | 24 VDC |
|                                              | Current              | 5 mA   |
|                                              | Hard silver contacts |        |
|                                              | Voltage              | 24 VDC |
|                                              | Current              | 50 mA  |

**Switching rating:** 250 V AC @ 6 A

**Electrical lifetime:** 50 000 cycles of operation (500 VAC, 10 A)

**Pollution degree:** 3

**Standards:** The switches comply with the “Standards for low-voltage switching devices” DIN EN IEC UL 60947-5-1

**Thermal current Ith:** Max. current as per EN IEC 60947-5-1 6 A

## MECHANICAL CHARACTERISTICS

|                            |                                                                                                                                                                                                                                                                                                                                                        |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Terminal:</b>           | Push-in terminal                                                                                                                                                                                                                                                                                                                                       |
| <b>Contact material:</b>   | Gold                                                                                                                                                                                                                                                                                                                                                   |
| <b>Switching system:</b>   | Slow-make switching element                                                                                                                                                                                                                                                                                                                            |
| <b>Switching system:</b>   | The double-break, slow-make switching element is equipped with one or two independent contact systems, acting as normally open or normally closed contact. The normally closed contact has forced opening. Slow-make contacts with forced action are ideal for high switch ratings.                                                                    |
| <b>Operating force:</b>    | 1 Normally closed approx. 2 N, 1 Normally open approx. 3 N                                                                                                                                                                                                                                                                                             |
| <b>Wire cross section:</b> | Wire cross-section 0.2 ... 1.0 mm <sup>2</sup> / AWG 24 to AWG 18<br>Skinning wire 8 mm<br>Max. number of wires: 2<br>stranded cables 0.2 ... 0.75 mm <sup>2</sup> / AWG 24 bis AWG 18<br>use stranded wires only with wire end ferrules of 8 mm length<br>Max. number of stranded cables: 2<br>Only one polarity is allowed on each side when wiring. |
| <b>Weight:</b>             | 0.026 kg                                                                                                                                                                                                                                                                                                                                               |

## AMBIENT CONDITION

|                               |                                                                                                                                       |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| <b>IP Protection:</b>         | IP20                                                                                                                                  |
| <b>Operating temperature:</b> | – 40 °C ... + 55 °C                                                                                                                   |
| <b>Storage temperature:</b>   | – 40 °C ... + 85 °C                                                                                                                   |
| <b>Shock resistance:</b>      | (single impacts, semi-sinusoidal) 300 m/s <sup>2</sup> , pulse width 18 ms, as per DIN EN 60068-2-27                                  |
| <b>Vibration resistance:</b>  | (sinusförmig) 100 m/s <sup>2</sup> bei 10 Hz...500 Hz, nach DIN EN 60068-2-6, Erhöhtes Breitbandrauschen nach DIN EN 61373, Klasse 1B |
| <b>Climate resistance:</b>    | Relative humidity 10 %rh ... 95 %rh (non-condensing) original packaging according to DIN EN IEC 60721-3-1 Class 1C1                   |

## CERTIFICATE

|                      |                                     |
|----------------------|-------------------------------------|
| <b>Approbations:</b> | CB (IEC 60947-5-1), cULus, DNV, VDE |
| <b>Conformities:</b> | CE, CCC, UKCA                       |
| <b>REACH:</b>        | REACH compliant                     |
| <b>RoHS:</b>         | RoHS compliant                      |

## OTHER

|                           |                                                                                                            |
|---------------------------|------------------------------------------------------------------------------------------------------------|
| <b>Short Description:</b> | Switching element - New Version, Slow-make switching element, 250 V AC @ 6 A, Gold, 2 NC, Push-in terminal |
| <b>Hints:</b>             | When using the switching element, the application guidelines must be observed.                             |


For the third switching element the terminal marking insert is to be ordered separately  
Operating temperature: Other temperatures on request  
A suitable enclosure is required for applications with increased protection requirements. In North America, the product must be installed in an enclosure in accordance with UL 50E Type 2 or higher.

**Special requirements:**

Special requirements for positive-opening auxiliary current switches  
Positive opening travel  
Minimum force  
Max. travel

Emerg  
Emerg  
which i  
Emerg

**Wiring diagrams:**



**Dimension drawings:**

