

Detectable cable markers - WMTB HF-D (40X12)R BU - 1255595

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Detectable cable markers, Roll, blue, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: Assembly with cable binders, cable diameter: ≥ 6 mm, lettering field size: 40 x 12 mm, Number of individual labels: 1000

Your advantages

- ✓ The halogen-free markers can be detected inductively
- ✓ Detectable cable marker WMTB HF-D ... for marking various cables and conductors in controller, system, and control cabinet manufacturing in the food industry
- ✓ When combined with the TM-RIBBON 105 BK 102 ink ribbon, the printing is highly resistant to solvents, aggressive cleaning agents, acetone, and ethanol
- ✓ The highly flexible material adapts to the conductors and cables



Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 362522
GTIN	4063151362522
Weight per Piece (excluding packing)	22.220 g
Custom tariff number	39204910
Sales Key	BG2311

Technical data

Dimensions

Length (b)	40 mm
Width (a)	12 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 105 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Detectable cable markers - WMTB HF-D (40X12)R BU - 1255595

Technical data

General

Note	Due to the differing detection properties of metal detectors, the installer/end user is to check suitability for the actual application
Color	blue
Type	Roll
Material	TPU
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1000
Number of individual labels per row	1
Mounting type	Assembly with cable binders
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Test for wipe resistance of inscriptions	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

Classifications

eCl@ss

eCl@ss 11.0	27281102
eCl@ss 9.0	27400401

ETIM

ETIM 7.0	EC001530
----------	----------

Accessories

Accessories

Ink ribbon

Detectable cable markers - WMTB HF-D (40X12)R BU - 1255595

Accessories

Ink ribbon - TM-RIBBON 105 BK 106 - 1255597



Ink ribbon, for roll printer for printing product groups WMTB HF-D, width: 105 mm, color: black