

## FEATURES

- **High chemical resistance:**  
Ensures durability and longevity in harsh environments
- **Maximum operating temperature of 280°C:**  
Suitable for high-temperature applications
- **Maximum operating pressure of 3000 kPa:**  
Capable of handling high-pressure systems
- **Rotary speed of 18 m/s:**  
Efficient performance in dynamic applications
- **Section size of 14 mm:** Fits a variety of gland and valve sizes

## RS PRO 8m Polytetrafluoroethylene Gland Packing

RS Stock No: 606-548



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO gland packing is designed for sealing applications in industrial environments. Made from high-quality polytetrafluoroethylene, it provides excellent resistance to chemicals and high temperatures, making it ideal for use in demanding conditions. The packing is suitable for both static and dynamic applications, offering reliable performance and longevity.

## General Specifications

Maximum Operating Pressure	3000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	18 m/s
Section	14 mm
Sub Type	Gland Packing

## Mechanical Specifications

Length	8 m
Material	Polytetrafluoroethylene

## Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, BAM, FDA, RoHS
---------------------	--------------------------------------