



ENGLISH

# Datasheet

## RS Pro 2 Way Tilt and Swivel Machine Vice

RS Stock No: 463-7331



### Specifications:

Heavy duty precision milling vices with swivel and tilt base.

Used in milling, shaping and drilling machines.

Swivel base is marked 360 degrees in 1 degree divisions.

Tilt capacity 90 degrees marked in 1 degree divisions

Parallelism of sliding surface to base 0.06mm / 100mm

Parallelism of jaws 0.05mm / 100mm

Squareness of fixed and moving jaws to upper slide surface 0.05mm / 100mm

Parallelism of base of bar clamped between jaws and sitting on the upper slide surface  
0.08mm / 100mm

Order Code	Manufacturers Code	Description
463-7331	52-832-160	2 Way Tilt and Swivel Machine Vice




ENGLISH

## Datasheet RS Pro 2 Way Tilt and Swivel Machine Vice

Max Jaw Opening mm	Jaw Width mm	Jaw Height mm	Angular Graduations
125	160	50	1 deg.

Fixing Bolt Size	Locating Key Width	Weight Kg
M16 x 55	18mm	33.5



A-Max mm	B mm	C mm	D-Min mm	D-Max mm	E mm	F mm	G mm	H mm	J mm	K mm
125	160	50	421	546	80	125	212	184	160	250