


VDE SCREWDRIVER
V 42
VDE HEXAGON ALLEN KEY for in-hex screws

- Acc. to DIN ISO 2936
- Particularly suitable for cable branch clamping rings
- Oil-hardened
- GEDORE vanadium special steel
- Individually tested, insulation up to 1000 V



mm	L ₁	L ₂	Code	No.
3	130	23.5	2324849	V 42 3
4	120	40.0	2324857	V 42 4
5	140	48.0	2324865	V 42 5
6	140	48.0	2324873	V 42 6
8	150	51.0	2324881	V 42 8
10	220	51.0	2324903	V 42 10
12	260	61.5	2324911	V 42 12

VDE 42 T
VDE HEXAGON ALLEN KEY WITH T-HANDLE for in-hex screws

- Individually tested, insulation up to 1000 V
- With Check-Tool insulation
- GEDORE chrome-vanadium steel 59CrV4



mm	mm	Code	No.
4	160	2661225	V 42 T 4
5	160	2661233	V 42 T 5
6	160	2661241	V 42 T 6
8	160	2661268	V 42 T 8
10	200	2661276	V 42 T 10
11	200	2661284	V 42 T 11
12	200	2661292	V 42 T 12

VDE 2170
VDE SCREWDRIVER for slotted head screws

- Individually tested, VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900, fully insulated blade
- Tip to DIN ISO 2380-1 form A
- 3-component handles Power-Grip³ with hanging hole
- Ergonomic handle design enables precise and fatigue-free working
- Positive-fit joint of handle and blade for optimum transmission of force
- Type of drive marked at end of the handle
- Blade from GEDORE molybdenum-vanadium-Plus tempered steel



mm	mm	mm	Code	No.
2.5	0.4	75	1612220	VDE 2170 2,5
3.0	0.5	100	1612239	VDE 2170 3
3.5	0.6	100	1612247	VDE 2170 3,5
4.0	0.8	100	1612255	VDE 2170 4
5.5	1.0	125	1612271	VDE 2170 5,5
6.5	1.2	150	1612298	VDE 2170 6,5
8.0	1.7	175	1612301	VDE 2170 8

VDE 2172
VDE SCREWDRIVER SLIM DRIVE for slotted head screws

- Individually tested, VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900, fully insulated blade
- 3-component handles Power-Grip³ with hanging hole
- Ergonomic handle design enables precise and fatigue-free working
- Positive-fit joint of handle and blade for optimum transmission of force
- Type of drive marked at end of the handle
- Ultra-small blade diameter yet with full mechanical and electrical safety
- No problems in reaching screws deeply embedded in screw shafts
- Blade from GEDORE molybdenum-vanadium-Plus tempered steel



mm	mm	mm	Code	No.
3.5	0.6	100	2824736	VDE 2172 3,5
4.0	0.8	100	2824744	VDE 2172 4
5.5	1.0	125	2824752	VDE 2172 5,5
6.5	1.2	150	2824760	VDE 2172 6,5

V 2160 MS PH
VDE SCREWDRIVER MAVO for cross-slotted head screws PH

- No-contact voltage finder and fitted magnetic field tester
- Voltage and magnetic fields are displayed in red and green, respectively
- The no-contact voltage finder detects energised conductors. The capacitive testing method can localise a break in the cable down to a few millimeters.
- The magnetic field tester examines the function of electro-magnetic switches and valves without having to place the switch out of service. Both permanent and alternating magnetic fields are displayed
- 3-component handles Power-Grip³
- Ergonomic handle design enables precise and fatigue-free working
- Positive-fit joint of handle and blade for optimum transmission of force
- Blade from GEDORE molybdenum-vanadium-Plus tempered steel
- Tested 1000 V

