

Eaton 061937

Catalog Number: 061937

Eaton xEnergy Safety Ci LV systems LV switchgear. MCB enclosure, +door, 3x15space units, HxWxD=375x375x150mm



General specifications

Product Name	Catalog Number
Eaton xEnergy Safety Ci MCB enclosure	061937
EAN	Product Length/Depth
4015080619376	150 mm
Product Height	Product Width
375 mm	375 mm
Product Weight	Compliances
3.88 kg	RoHS conform
Certifications	
EN 61439-2	
EN 62208	

Product specifications

Special features

Metric cable entry knockouts
in all sides

Housings for e.g. built-in
devices MCB, RCD, RCBO,
AFDD

Transparent door for
operator access to devices
fitted

Metal mounting rail for
snapping on devices

1 x Blanking strip for unused
mounting locations

Protective shroud with
inscription label

PE/N combi-plug-in
terminals

Fixing straps for wall fixing

Sealable cover fasteners

Type

MCB individual enclosures

Prepared enclosure

xEnergy Safety Ci

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility.

10.13 Mechanical function

Meets the product standard's requirements.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

Resources

Brochures

[eaton-xenergy-safety-ci-subway-line-success-story-en-us.pdf](#)

[eaton-xenergy-safety-ci-enclosure-brochure-br014001en-en-us.pdf](#)

Catalogs

[eaton-xenergy-ci-safety-catalog-ca015006en-en-us.pdf](#)

Drawings

[eaton-distribution-boards-enclosure-xenergy-safety-ci-mcb-enclosure-dimensions-003.eps](#)

[eaton-lighting-enclosure-xenergy-safety-ci-mcb-enclosure-dimensions-003.eps](#)

Installation instructions

[IL015090ZU](#)

mCAD model

[ae_i44e_t.dwg](#)

[ae_i44e_t.stp](#)

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Lower part: 960 °C / cover: 850 °C; meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Not relevant to indoor installations.

10.2.5 Lifting

20 kg per enclosure with support frame and lifting aid met; assembled and secured as per the latest applicable instruction leaflet.

10.2.6 Mechanical impact

IK10

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

IP65

10.4 Clearances and creepage distances

Is the panel builder's responsibility.

10.5 Protection against electric shock

Protection class 2, therefore not applicable.

10.6 Incorporation of switching devices and components

Is the panel builder's responsibility.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

$U_i = 1000 \text{ V AC}$

10.9.3 Impulse withstand voltage

8 kV

10.9.4 Testing of enclosures made of insulating material

Meets the product standard's requirements.

Enclosure material

Plastic

Accessory/spare part type

MCB individual enclosures

Built-in height

0 mm

Built-in width

0 mm

Unit type

Stand-alone device

Built-in depth

100 mm

Heat diss. ambient 35°C delta T:20°C wall mount individ. encl. top (IEC 60890)

25 W

Heat diss. ambient 35°C delta T: 20°C wall mount middle encl. top (IEC 60890)

23 W

Heat diss. ambient 35°C delta T:20°C wall mount starting encl. top (IEC 60890)

24 W

Closure type

Other

Cover/door color

Transparent

Cover/door model

Closed

Cover/door type

Door

Transparent

Single

RAL-number

7035

Width in number of modular spacings

15

Color

Gray

Number of rows

3

Number of module space units (total)

45

Degree of protection

IP65

Number and capacity of terminal (PE and N)

On each 3 x (2.5 - 25 mm²)

On each 21 x (0.5 - 4 mm²)

Functions

Prepared enclosure

Mounting method

DIN-rail

Surface mounted (plaster)

Heat diss. ambient 35°C delta T:35°C wall mount individ. encl.
top (IEC 60890)

51 W

Heat diss. ambient 35°C delta T: 35°C wall mount middle encl.
top (IEC 60890)

45 W

Heat diss. ambient 35°C delta T:35°C wall mount starting encl.
top (IEC 60890)

48 W

Internal depth

150 mm



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia