




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Number of Rows: **1**

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	2
Number of Loaded Positions	2
Number of Power Positions	2
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	2



Number of Rows	1
----------------	---

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
Mating Pin Diameter	2.2 mm[.087 in]
Contact Underplating Material Thickness	1.27 – 1.79 µm[50 – 70 µin]
Contact Size	2.2mm
Contact Mating Area Plating Material Thickness	3.81 – 5.08 µm[150 – 200 µin]
PCB Contact Termination Area Plating Material Thickness	3.81 – 5.08 µm[150 – 200 µin]
Contact Shape & Form	Round
Contact Layout	Inline
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Pre-Tin
Contact Mating Area Plating Material	Pre-Tin
Contact Type	Pin
Contact Current Rating (Max)	12 A

Termination Features

Termination Post & Tail Diameter	1.57 mm[.062 in]
Termination Post & Tail Length	3.56 mm[.14 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Tab
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With



Housing Features

Mating Entry Location	Top
Housing Material	Nylon
Centerline (Pitch)	6.35 mm[.25 in]

Dimensions

Connector Width	7.62 mm[.3 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Height	13.97 mm[.55 in]
Connector Length	13.97 mm[.55 in]
Profile Height from PCB	14.73 mm[.58 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	200
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 794584-2 05P UMNL SOC HDR ASS POL BLACK	 TE Part # 1586077-1 03P UMNL PIN HDR ASSY W/O DRNS	 TE Part # 1969804-1 04P UMNL HDR ASSY, SCKT V0 GW	 TE Part # 1586134-1 05P UMNL PIN HDR V2 NATL NDH
 TE Part # 2029002-1 09P UMNL HDR ASSY PC, NDH	 TE Part # 6-641968-1 4P UMNL PIN HDR ASS POL VO BLU	 TE Part # 794876-1 02P UMNL PIN HDR ASSY POL 94VO	 TE Part # 926305-6 UNML4WAY CAP
 TE Part # 794783-3 04P UMNL HDR ASSY, BLACK LF	 TE Part # 1-480703-2 04P UMNL CAP HSG RED	 TE Part # 1969803-1 03P UMNL PIN HDR ASSY NATL, PIN V0 GW	 TE Part # 1586163-1 04P UMML PIN HDR 94VO NDH



TE Part # 1-350780-9
04P UMNL V0 CAP HSG BLACK

TE Part # 1586090-1
06P UMNL PINHDR NO DRAIN HOLE

TE Part # 1586137-1
02P UMNL PIN HDR POL NAT NDH

TE Part # 1-480703-0
04P UMNL CAP HSG NATL

TE Part # 794783-1
04P UMNL HDR ASSY, BLACK

TE Part # 794880-1
09P UMNL PIN HDR ASSY 94VO

TE Part # 794878-1
03P UMNL PIN HDR ASSY 94VO

TE Part # 1969829-1
06P UMNL SOK HDR Hsg 94VO GW

Also in the Series | Universal MATE-N-LOK

Circular Power Connectors(2)

Connector Contacts(208)

Connector Hardware(12)

Power Contacts(208)

Rectangular Power Connectors(651)

Standard Circular Connectors(1)

Customers Also Bought

TE Part #1-770621-0
12P MINI UMNL DBL ROW HDR ASSY

TE Part #5-2149531-1
STRADA MESA, RC, HF, 000, 000, 12, SN, N, NA

TE Part #1-770873-0
03P MINI UMNL HDR ASSY SN

TE Part #2-5747707-0
15 RCPT SP/FMS BRDLK



TE Part #282828-4
[TERMI-BLOK HEADER,ASSY90 4P.](#)

TE Part #643749-1
[06P UMNL HDR ASSY W/O DRNS](#)

TE Part #2057426-3
[IMP100S,H,V2P10C,UG,OEW46,5.5](#)

TE Part #CAT-J04-APHH
[AMPSEAL PCB Right-Angle Headers](#)

TE Part #1-84981-0
[1MM FFC SMT H ASSY 10P EMBOSS](#)

Documents

Product Drawings

[02P UMNL PIN HDR W/O DRNS V2](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1586076-1_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1586076-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1586076-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL](#)

English