

Features

- Excellent abrasion and corrosion properties for increased durability.
- Good flexibility for ease of use.
- Manufactured from cadmium and silicone-free materials using a special low toxic, odourless PVC formulation that can reduce the taint of drinking water.
- EU No.10/2011 compliant for food contact applications.
- RoHS 3 compliant.
- Suitable for use with alcohol, petrol, oils, greases and solvents.
- Highly resistant to a wide range of acids and alkalis.
- Service temperature = -15°C to + 60°C.
- NSF51 + NSF61 approved for the transfer of drinking water

RS PRO Hose Pipes & Flex Tubes

RS Stock No.: 0336822



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Clear PVC hose suitable for both low pressure food and industrial applications. It is manufactured from the highest quality, low-toxic materials to give excellent clarity, flexibility and durability over a wide temperature range.

Glass clear transparency for easy visibility.

- Excellent abrasion and corrosion properties for increased durability.
- Good flexibility for ease of use.
- Manufactured from cadmium and silicone-free materials using a special low toxic, odourless PVC formulation that can reduce the taint of drinking water.
- EU No.10/2011 compliant for food contact applications.
- RoHS 3 compliant.
- Suitable for use with alcohol, petrol, oils, greases and solvents.
- Highly resistant to a wide range of acids and alkalis.
- Service temperature = -15°C to + 60°C.
- NSF51 + NSF61 approved for the transfer of drinking water
-

Applications:

- Medical
- Scientific
- Pharmaceutical
- Industrial

General Specifications

Hose Pipe / Flexible Tube	Flexible Tube
Colour	Clear
Features	Flexible
Series	RS PRO C
Inner Diameter	22mm
Outer Diameter	28mm
Material	PVC
Hose Pipe Action	Transfer
Maximum Working Pressure	4bar
Suitable Application	Biopharmaceutical, Chemical, Food & Beverage, Medical
Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+60°C
Length	30m
Reinforced	No
Bend Radius	252mm
Standards Met	NSF 61; NSF 51