

DETECTAMET

Technical Data Sheet

Document Reference	146
Date of Issue	23 rd Oct 2024
Revision Number	001
Date of Last Revision	23 rd Oct 2024

146 Permanent Marker



Technical Data Sheet Applicable To:

146-A06-P0*-A07	Permanent Marker Non Retractable Bullet Tip (All Colours)
146-A06-P0*-A08	Permanent Marker Non Retractable Chisel Tip (All Colours)
146-A05-P0*-A07	Permanent Marker Retractable Bullet Tip (All Colours)
146-A05-P0*-A08	Permanent Marker Retractable Chisel Tip (All Colours)

Industry Usage:

These non-retractable permanent marker pens come in blue housing with a bullet or chisel tip.

Features and Benefits:

- Metal Detectable & X-Ray Visible
- Manufactured from EU and FDA food contact approved detectable polymer
- Usage Temperature: -10°C to +35°C (14 to 95°F)
- Lid attaches to end of pen

Material and Compliance Information:

- Length: 139.69mm (5.49")
- Thickness: 17.08mm (0.67")
- Thickness with clip: 19.96mm (0.78")
- Bullet tip: 3mm to 4mm (0.11 – 0.15")
- Chisel tip: 1.5mm to 4mm (0.05 – 0.15")

We confirm that the above mentioned products are suitable for use in contact with all food types and are in conformity with the applicable requirements of the following regulations and standards:

- Regulation (EC) no.1935/2004 on Materials and Articles intended to come into contact with food.
- Commission Regulation (EU) No.10/2011 on Plastic materials intended to come into contact with food including its updates Regulation 1282/2011 and Regulation 1183/2012.
- Regulation (EC) no. 2023/2006 on Good Manufacturing Practice for materials and articles intended to come into contact with food.
- Council of Europe Resolution AP 89/1 on the use of Colorants in Plastic Materials coming into contact with food.
- US FDA 21 CFR 177.1520 (Olefin polymers) with colorants and additives cleared for use through listing in 178.3297 (Colorants for polymers), 178.2010 (antioxidants and/or stabilisers for polymers, or other respective parts of the FDA regulations.

Migration test data obtained under short-term repeat use test conditions (6dm²/kg food) has demonstrated that levels of overall migration and specific migration of additives from these products will not exceed the legal limits with all food types.

Test Simulants	Food Types	Testing Condition
A-C, D1, D2 of Regulation No. 10/2011 for Plastic Materials and Articles in contact with food.	All dry, aqueous, acidic, alcohol and fatty foods.	2 hours at 70c, Repeat use. Test OM3 of regulation 10/2011

Dual-use food additives may be present but any migration into food will be minimal.

This compliance statement is based on information supplied by the polymer and pigment manufacturers, migration testing according to Regulation 10/2011, migration modelling and quality control systems in place at Detectamet.

Supporting documents are available and can be disclosed to the competent authority on request.

REACH – No substances of very high concern (SVHC) above the 0.1% weight (w/w) threshold limit are present in the materials.

These products are Xylene free.

Retractable Permanent Marker Ink

1. Identification

Product Name: Permanent Marker

Colours: Blue, black, red and green.

2. Hazard Identification

Product is not hazardous under normal use conditions

3. Composition

N-propanol, iso propyl alcohol glycol, dyers, pigment, resin, additives

4. First Aid Measures

Inhalation: Not an inhalation hazard under normal use conditions

Skin contact: Wash with soap and water

Eye contact: Flush with water for at least 15 minutes. If irritation persists, consult a physician.

Ingestion: If large amount is ingested seek medical attention.

5. Firefighting Measures

Flash point: Not determined

Extinguishing media: As appropriate for surrounding area

Special firefighting measures: None

Unusual fire and explosion hazards: Acrid smoke, fumes

6. Accidental Release Measures

Incase of spill or accidental release: Wipe up with absorbent material

7. Handling and Storage

Handling: Do not shake pen

Storage: Keep cap on pen or pen retracted when not in use

8. Exposure Controls and Personal Protection

Eye protection: Not under normal use conditions

Clothing: Not under normal use conditions

Respirator: Not under normal use conditions

Ventilation: Not under normal use conditions

9. Physical and Chemical Properties

For ink unless otherwise specified

Boiling Point: N/A

Specific Gravity: N/A

Vapor pressure: N/A

Solubility in water: Insoluble

Evaporation rate: N/A

Appearance/Odour: Coloured liquid, slight odour.

10. Stability and Reactivity

Stability: Stable

Conditions to avoid: N/A

Chemical incompatibility: N/A

Hazardous decomposition: N/A

Hazardous polymerization: Will not occur

11. Toxicological Information

See section 2: Hazard identification for any hazards

12. Ecological Information

Not available.

13. Disposal Considerations

Dispose in accordance with federal, state and local regulations

14. Transport Information

DOT Not regulated as a hazardous material for shipping.

IATA Not regulated as a hazardous material for shipping.

IMO Not regulated as a hazardous material for shipping.

15. Regulatory Information

US All ingredients in this product are listed on or exempt from reporting under the Toxic Substances Control Act (TSCA)

Canada All ingredients in this product are listed on or exempt from reporting under the Domestic Substances List (DSL) or Non-Domestic Substances List (NDSL)

16. Other Information

Health: N/A

Flammability: N/A

Reactivity: N/A

Personal protection: N/A

0=minimul / 4=severe

No warranty is given or implied with respect to this information or patent infringement. Detectamet Ltd do not accept liability for loss or damage arising from the use of this information. Results are based on a test sample, our general experience and information from suppliers. Data and results may be confirmed by the buyer by testing for its intended conditions of use.

Safety You Detect

detectamet.global