


angle seat valve

VZXA-B-TS6-13-M2-V13T-30-K-46-17-V4

Part number: 8060527

FESTO

Modular, pneumatically actuated angle seat valve in stainless steel.
Under seat version, safety position closed, G thread, nominal width DN13.



Data sheet

Feature	Value
Design structure	Poppet valve with piston actuator
Type of actuation	pneumatic
Assembly position	Any
Mounting type	Line installation
Line connection	G $\frac{1}{2}$ threaded collar to DIN ISO 228
Valve function	2/2
Flow direction	non reversible
Medium pressure	0 ... 30 bar
Type of reset	mechanical spring
Type of piloting	With external control
Pneumatic connection	Female thread G1/8
Operating pressure	5 ... 10 bar
Medium	Vapour Mineral oil-based hydraulic oil Inert gases Mineral oil Water Filtered compressed air, degree of filtration 200 μ m Neutral fluids
Flow direction	Below valve seat, for gaseous and liquid media
Control of the medium	On/off operation
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Max. viscosity	600 mm ² /s
Medium temperature	-10 ... 180 °C
Ambient temperature	0 ... 60 °C
Flow rate Kv	6 m ³ /h
Materials note	Contains PWIS substances Conforms to RoHS
Material process valve housing	Stainless steel casting
Material number, process valve housing	1.4409
Material seals	FPM
Material spindle seal	PTFE
Material seat seal	PTFE
Product weight	1,830 g
Authorisation	CRN
CE mark (see declaration of conformity)	to EU directive for machinery
Certificate issuing department	CRN0C20829.5C TÜV 968/V 1039.00/18
Safety Integrity Level (SIL)	SIL 2
Probability of Failure per Hour in [1/h].	1.36E-07
PFD (Probability of Failure on Demand)	5.95E-04
Actuator size	46 mm
Stroke	17 mm

Feature	Value
Control function	Closed via spring force, NC
Position detection	With mechanical indicator
Material drive housing	Stainless steel casting
Material number, actuator housing	1.4408
Storage temperature	-10 ... 60 °C
Protection class	IP65 IP67 IP69K
Material piston rod	High alloy steel, non-corrosive
Material cover	Stainless steel casting