



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Grommet**
Primary Product Material: **Silicone Rubber**
Primary Product Color: **Natural**
Operating Temperature Range: **-20 – 220 °C [-4 – 428 °F]**

Features

Product Type Features

Strain Relief Accessory Type	Grommet
------------------------------	---------

Body Features

Primary Product Material	Silicone Rubber
Primary Product Color	Natural

Usage Conditions

Operating Temperature Range	-20 – 220 °C[-4 – 428 °F]
-----------------------------	---------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold:



Octamethylcyclotetrasiloxane (D4) (.55% in Component Part)
Dodecamethylcyclohexasiloxane (D6) (.3% in Component Part)
Decamethylcyclopentasiloxane (D5) (.59% in Component Part)

Article Safe Usage Statements:
Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2299959-1
TRAY PACKAGE.THERMOCOUPLE
CONN KTYPE REC

Also in the Series | Dynamic Series Thermocouple Connector



Connector Caps & Covers(1)



Connector Strain Relief(1)



Insertion & Extraction Tools(1)



Wire-to-Board Connector Assemblies & Housings(3)

Customers Also Bought






TE Part #201311-1
FEMALE BLOCK MIN. RECT.



TE Part #207234-1
UNASSM JS KIT,M SERIES



TE Part #207235-1
UNASSM JS KIT,M SERIES



TE Part #91569-1
CCII POWER DBL LOCK L REC TAB 20-16 ASSY



TE Part #91567-1
CCII POWER DBL LOCK S REC TAB 26-22 ASSY



TE Part #T4140012041-000
M12,REAR MOUNTING,MALE,A CODE,4P



TE Part #234914-1
EXT TOOL FOR POWER DBL LOK TAB



TE Part #201092-4
SER. "M" JACKSCREW STUD KIT



TE Part #91561-1
CCII D-3 3L REC TAB 16-14 ASSY



TE Part #1762130-1
SAHT DYNAMIC D4-M 16-14 ASSY

Documents

Product Drawings

THERMOCOUPLE CONN K-TYPE 2P.GROMMET

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2295225-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2295225-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2295225-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1-1773895-2_THERMOCOUPLE_FLYER

English

Product Specifications
Product Specification

Japanese