

# PRODUCT DATASHEET

## ST5HO49-UN 26 W/3000K 1449 mm

SubstiTUBE T5 HO UN | LED tubes for electronic high frequency control gears and AC mains



---

### AREAS OF APPLICATION

- Supermarkets and department stores
- Industry
- Public buildings, reception areas, offices, corridors, etc.
- General illumination within ambient temperatures from -20...+50 °C

---

### PRODUCT BENEFITS

- No bending thanks to glass technology
- Also suitable for operation at low temperatures
- High luminous flux for sophisticated lighting tasks

---

### PRODUCT FEATURES

- Tube made of glass
- Type of protection: IP20
- Lifetime: up to 60,000 h
- Compatible with many common electronic control gears (see also compatibility list) and line voltage
- High color consistency:  $\leq 5$  SDCM



## TECHNICAL DATA

### Electrical data

<b>Rated wattage</b>	26.00 W
<b>Nominal voltage</b>	220...240 V
<b>Operating frequency</b>	50...60 Hz <sup>1)</sup>
<b>Nominal wattage</b>	26.00 W
<b>Nominal current</b>	0.12 A <sup>2)</sup>
<b>Type of current</b>	AC
<b>Max. lamp no. on circuit break. 10 A (B)</b>	36
<b>Max. lamp no. on circuit break. 16 A (B)</b>	59
<b>Total harmonic distortion</b>	< 20 %
<b>Power factor <math>\lambda</math></b>	> 0.90

<sup>1)</sup> 40-80KHz for ECG (HF)

<sup>2)</sup> 270-600 mA for ECG (HF)

### Photometrical data

<b>Rated color temperature</b>	3000 K
<b>Nominal luminous flux</b>	3600 lm
<b>Rated luminous flux</b>	3600 lm
<b>Lumen main.fact.at end of nom.life time</b>	0.70
<b>Light color (designation)</b>	Warm White
<b>Color temperature</b>	3000 K
<b>Luminous flux</b>	3600 lm
<b>Color rendering index Ra</b>	85
<b>Standard deviation of color matching</b>	$\leq 5$ sdc <sub>m</sub>

### Light technical data

<b>Starting time</b>	< 0.5 s
<b>Warm-up time (60 %)</b>	< 0.50 s
<b>Rated beam angle (half peak value)</b>	160.00 °

Dimensions & weight



<b>Length with base excl. base pins/connection</b>	1449.00 mm
<b>Tube diameter</b>	16 mm
<b>Base diameter</b>	17.0 mm
<b>Product weight</b>	190.00 g
<b>Overall length</b>	1449 mm

Temperatures & operating conditions

<b>Ambient temperature range</b>	-20...+50 °C
<b>Maximum temperature at tc test point</b>	85 °C

Lifespan

<b>Lifespan</b>	60000 h
<b>Nominal lamp life time</b>	60000 h
<b>Rated lamp life time</b>	60000 h
<b>Number of switching cycles</b>	200000

Additional product data

<b>Base (standard designation)</b>	G5
<b>Mercury-free</b>	Yes

Capabilities

<b>Dimmable</b>	No
-----------------	----

Certificates & standards

<b>Type of protection</b>	IP20
<b>Standards</b>	CE
<b>Energy efficiency class</b>	A++
<b>Energy consumption</b>	26 kWh/1000h


Country-specific categorizations

<b>Order reference</b>	ST5HO49-1.5M 26
------------------------	-----------------

Logistical data

<b>Temperature range at storage</b>	-20...+80 °C
-------------------------------------	--------------

Light Distribution



LDC typ polar

**SAFETY ADVICE**

Not suitable for operation with conventional control gear  
 Operation in outdoor applications in suitable damp-proof luminaires possible according to data sheet and installation instruction.

**LOGISTICAL DATA**

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075137967	Sleeves 1	1465 mm x 20 mm x 25 mm	223.00 g	0.73 dm <sup>3</sup>
4058075137974	Shipping carton box 10	1495 mm x 157 mm x 89 mm	2822.00 g	20.89 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

**REFERENCES / LINKS**

For current information see

▶ [www.ledvance.com/substitute](http://www.ledvance.com/substitute)

---

**LEGAL ADVICE**

When used to replace a T5 fluorescent lamp, the total energy efficiency and light distribution depends on the design of the lighting system.

---

**DISCLAIMER**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.